

## Eaton XT IEC contactor

### XTCE012B10B

#### Dimensions:

- **Height:** 3.07 IN
- **Length:** 1.81 IN
- **Width:** 2.76 IN

**Weight:** .5 LB

**Warranties:** No Data

#### Specifications:

- **Amperage Rating:** 12A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

#### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_B 3D Inventor](#)
- [XTCE\\_B 3D Model Xchange](#)
- [XTCE\\_B AutoCAD 2D Footprint](#)
- [XTCE\\_B 2D PDF](#)
- [XTCE\\_B 2D Drawing Xchange](#)
- [Global Data Sheet - XTCE012B10B](#)
- [Eaton Specification Sheet - XTCE012B10B](#)

#### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



