

## Eaton XT IEC contactor

### XTCE012B10T

#### Dimensions:

- **Height:** 2.67716535 IN
- **Length:** 4.92913386 IN
- **Width:** 1.77165354 IN

#### Weight:.5 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

#### Specifications:

- **Amperage Rating:** 12A
- **Coil Voltage:** 24 Vac, 50-60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

#### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_B AutoCAD 2D Footprint](#)
- [XTCE\\_B 2D PDF](#)
- [XTCE\\_B 3D Inventor](#)
- [XTCE\\_B 3D Model Xchange](#)
- [XTCE\\_B 2D Drawing Xchange](#)
- [Global Data Sheet - XTCE012B10T](#)
- [Eaton Specification Sheet - XTCE012B10T](#)

#### Certifications:

- UL Listed
- CSA Certified



- IEC 60947
- EN 60947

**Product compliance:**

- RoHS Compliant
- CE Marked

---

© 2016 Eaton. All rights reserved.