

## Eaton XT IEC contactor

### XTCE032C10B

#### Dimensions:

- **Height:** 2 IN
- **Length:** 4 IN
- **Width:** 3.5 IN

#### Weight:.5 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

#### Specifications:

- **Amperage Rating:** 32A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 3, 5, 5/ 10, 10, 20, 25 hp  
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

#### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_C 2D PDF](#)
- [XTCE\\_C 2D Drawing Xchange](#)
- [XTCE\\_C 3D Model Xchange](#)
- [XTCE\\_C AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCE032C10B](#)
- [Global Data Sheet - XTCE032C10B](#)

#### Certifications:

- UL Listed
- CSA Certified
- IEC 60947



- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.