

Eaton XT IEC mini contactor

XTMC9A10T

Dimensions:

- **Height:** 2 IN
- **Length:** 2 IN
- **Width:** 2.5 IN

Weight:.4 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 8.80A
- **Coil Voltage:** 24 Vac, 50-60 Hz
- **Contact Configuration:** 1NO
- **Continuous Ampere Rating:** 20A
- **Frame Size:** 45 mm mini
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing mini contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTMC 2D Drawing Xchange](#)
- [XTMC 2D PDF](#)
- [XTMC 3D Inventor](#)
- [XTMC AutoCAD 2D Footprint](#)
- [XTMC AutoCAD 2D Footprint \(mm\)](#)
- [XTMC 3D Model Xchange](#)
- [XT IEC power control 580-2600A vacuum contactors](#)
- [Eaton Specification Sheet - XTMC9A10T](#)



- [Global Data Sheet - XTMC9A10T](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947
- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.