

Eaton, 22.5 mm RQM Compact Pushbutton

C22-DR-G-K11

Dimensions:

- **Height:** 2.15 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

Weight:.06 LB

Notes:Maintained pushbuttons can be converted in the field to momentary operation by switching the locking ring, which is accessible through the side of the operator body.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Pushbutton
- **Action:** Maintained
- **Actuator:** Flush button
- **Actuator Color:** Green
- **Actuator Material:** Plastic actuator
- **Bezel:** Silver
- **Contact Configuration:** 1NO - 1NC
- **Enclosure:** IP 67, IP69K
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Nema Rating:** NEMA 4X, 13
- **Operating Cycles:** 1,000,000 operations
- **Size:** 22.5 mm
- **Product Category:** Flush pushbutton
- **Series:** C22 Series

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator](#)



Interface and Connectivity Solutions

- C22-PVT45P 2D Drawing Xchange
- C22-PVT45P 3D Inventor
- C22-PVT45P AutoCAD 2D Footprint (mm)
- C22-PVT45P AutoCAD 2D Footprint
- C22-PVT45P 2D PDF
- C22-PVT45P 3D Model Xchange
- C22 Pilot Devices
- Eaton Specification Sheet - C22-DR-G-K11

Certifications:

- IEC 60947
- UL Listed
- EN 60947
- CSA Certified

Product compliance:

- DIN VDE 0600