

## Eaton XT IEC contactor

XTCE007B10E

### Dimensions:

- **Height:** 2 IN
- **Length:** 3 IN
- **Width:** 3 IN

**Weight:** .5 LB

**Notes:** Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

### Specifications:

- **Amperage Rating:** 7A
- **Coil Voltage:** 208 Vac, 60 Hz
- **Contact Configuration:** 1NO
- **Frequency Rating:** 60 Hz
- **Max Hp Rating:** 0.25, 0.75, 1/ 1.5, 2, 3, 5 hp  
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_B 3D Model Xchange](#)
- [XTCE\\_B AutoCAD 2D Footprint](#)
- [XTCE\\_B 2D Drawing Xchange](#)
- [XTCE\\_B 3D Inventor](#)
- [XTCE\\_B 2D PDF](#)
- [Eaton Specification Sheet - XTCE007B10E](#)
- [Global Data Sheet - XTCE007B10E](#)

### Certifications:

- UL Listed
- CSA Certified
- IEC 60947



- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.