

Eaton XT IEC contactor

XTCE015B10B

Dimensions:

- **Height:** 2 IN
- **Length:** 3 IN
- **Width:** 3 IN

Weight: .3 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 15A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_B 3D Model Xchange](#)
- [XTCE_B AutoCAD 2D Footprint](#)
- [XTCE_B 2D Drawing Xchange](#)
- [XTCE_B 3D Inventor](#)
- [XTCE_B 2D PDF](#)
- [Global Data Sheet - XTCE015B10B](#)
- [Eaton Specification Sheet - XTCE015B10B](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947



- EN 60947

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.