

HMI-PLC XV Operator Interface

XV-102-D6-57TVRC-10

Dimensions:

- **Height:** 12 IN
- **Length:** 5 IN
- **Width:** 12 IN

Weight: 3 LB

Notes: All 1xx performance class units have 400MHz processor, 64 MB DRAM, 1x10/100 Ethernet, and 1x USB device.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Base Unit:** Retentive memory, USB host, RS-232
- **Bezel:** Blank front
- **Communication:** CANopen
- **Display:** 5.7 in TFT resistive touch (VGA)
- **Operating System:** XSoft-CoDeSys/Galileo
- **Serial Interface:** RS-232, RS-485

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XV and XP Series Operator Interfaces Product Aid - PA04801003E](#)
- [Eaton Specification Sheet - XV-102-D6-57TVRC-10](#)

Certifications:

- UL Listed
- cULus Listed

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.