



DIGITAL AUDIO FOUR-ROOM, MULTI-SOURCE KIT, WHITE

AU7254-WH | [On-Q](#)

FEATURES & BENEFITS

The AU7254-WH is a four-room, multi-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a four-room Digital Audio system with digital and analog source accessibility, this kit comes complete with (4) AU7010-WH Digital Audio Amplified Keypads, (1) AU7000 Digital Audio Distribution Module, (1) AU7001 Digital Audio Input Module, (1) AU7007-WH Digital Audio Global Source Input, (1) AU7100-WH Digital Audio Bluetooth Receiver, (1) PW1020 Digital Audio Power Distribution Module, (1) PW1060 Power Supply, and (1) PW7760 Power Supply.

Check out the [Digital Audio mobile app](#).



- Comes complete with all core components for a four-room, multi-source Digital Audio System with digital and analog source accessibility
- Built-in access to streaming services including, Spotify, iHeartRadio, Pandora, Napster, SiriusXM, and Tuneln
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Offers global access to analog source equipment
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a four-room, multi-source Digital Audio System with digital and analog source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Includes the Digital Audio Bluetooth Receiver (AU7100-WH) to wirelessly connect any Bluetooth enabled device, like iPods, smart phones, and tablets to your system
- Simple setup using smartphone or tablet, no PC required
- Available in a two-room kit (AU7152-WH)

*Streaming services subject to geographic availability. Service subscriptions may be required.

SPECIFICATIONS

GENERAL INFO

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.
Color: White
Size: 11.25" x 7.75" x 14.5"
Termination: 1264.22 cu. in.
Connection Type: RJ45 connections and removeable pheonix screw down terminals
Type: Low Voltage, Audio System
Special Features: 4-Zone, 2-Source Digital Audio System
Style: Decorator Keypad; Structured wiring cabinet (not included)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
FCC Standard: Yes
UL Standard: Yes

DIMENSIONS

Depth (Metric): 368.3mm
Depth (US): 14.5"
Width (Metric): 285.75mm
Width (US): 11.25"
Primary Packaging Weight (Metric): 2.99 kg
Product Weight (Metric): 2.99 kg
Product Weight (US): 6.6 lbs
Volume: 1264.22 cu. in.
Weight: 6.6 lbs
Height: 7.75"

TECHNICAL INFORMATION

Connection Method: Ethernet network
Mounting: Wall Mount/Enclosure Mount
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply
Supported Standards: FCC, UL, RoHS
Watts: 20W 8Ω
Connection Location: Data Control Interface: Ethernet/Digital Keypad

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA