



## LS TRADEMASTER®; SINGLE-POLE/3-WAY PRESET DIMMER W/ SINGLE-POLE/3-WAY, 3-SPEED DE-HUMMER FAN CONTROL, WHITE

LSCLDC163PW | [Pass & Seymour](#)

### FEATURES & BENEFITS

The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.



- CFL/LED dimmable bulb compatible (except for 0-10V LED drivers).
- Single pole/3-way versions.
- Unique integrated single pole/3-way dimmer with fan speed control.
- Rating: 150W LED & CFL; 300W Incandescent. 1.6A (Fan Control) 120VAC 60Hz.

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Product Series: LS TradeMaster  
Type: CFL/LED  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes

#### DIMENSIONS

Depth (US): 1.28"  
Height (US): 4.19"  
Width (US): 2.50"

#### TECHNICAL INFORMATION

Volts (AC): 120  
Watts: 450