



120V MULTI-LOCATION REMOTE DIMMER, WHITE

HMRW | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

This dimmer is multi-location dimming compatible with 3-way wiring for simple installation.

radiant® Screwless Wall Plate not included.



- Convenient operation - combines ON/OFF paddle switch with a separate slider for dimming control.
- White LED glows when OFF to make dimmer easy to find in the dark.
- Constant memory returns lights to previous level after a power failure
- CFL/LED dimmable-bulb compatible (with the exception of 0 - 10v LED drivers).
- No derating required in multi-gang applications.
- Rating: 450W LED & CFL; 700W Incandescent; 120VAC 60Hz.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Number Of Poles: Single Pole/3-Way

Style: Rocker

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Standard: Yes

TECHNICAL INFORMATION

Compatible Power Supplies: Apple

Volts: 120

Volts (AC): 120 VAC, 60Hz

Watts: 450

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA