



MULTI-LOCATION MASTER DIMMER, TRI-COLOR

HCL453PMMTC | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

Pair this multi-location dimmer with up to nine remote dimmers ([HMRTC/HMRW](#)) for multi-way dimming.

radiant® Screwless Wall Plate not included.



RoHS



LEED
CONTRIBUTION

- Part of the all-new radiant® collection.
- Convenient operation - combines ON/OFF paddle switch with a separate slider for dimming control.
- White LED glows when OFF to make dimmer easy to find in the dark.
- Compatible with Incandescent, CFL/LED (with the exception of 0 - 10v LED drivers) and MLV dimmable bulbs.
- Single Pole and 3-Way Operation.
- No derating required in multi-gang applications.
- Rating: 450W CFL/LED; 700W Incandescent; 700VAC MLV
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)

Number Of Poles: Single Pole/3-Way

Style: Rocker

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 184
CSA Standard: Yes
cULus: Yes
UL Standard: Yes

DIMENSIONS

Depth (US): 1.25"
Height (US): 4.25"
Width (US): 1.75"

TECHNICAL INFORMATION

Volts: 120
Watts: 450

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA