

# STE402NP/STE403NP

ELECTRONIC THERMOSTAT – SINGLE PROGRAMMING

4000 W



ALSO AVAILABLE  
STE403NP – 347 V MODEL



## PRACTICAL AND EFFICIENT!

The STE402NP electronic thermostat allows you to precisely control the temperature. It has a Security mode that lets you program a maximum temperature setpoint. It's simple and safe!



**SIMPLE TO USE  
AND INSTALL**



**GREAT POWER**  
4000 W



**INCREASED SAVINGS  
AND COMFORT**  
INCOMPARABLE ACCURACY



**BACKLIT SCREEN†**  
CAN BE USED AS A NIGHTLIGHT



**ELECTRICITY SAVINGS**  
ENERGY SAVINGS OF 10-15%  
DEPENDING ON USE\*

### COLOUR

- white

### FINISH

- molded plastic

### WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V
- 350 W to 4600 W @ 277 V (STE403NP)
- 400 W to 5750 W @ 347 V (STE403NP)

### CONTROL

- two- or four-wire connection
- acts like a programmable thermostat by automatically lowering the temperature once per 24-hour period (Single programming mode)

- compatible with forced-air units (Fan mode)
- frost-free warning
- lock option at a maximum temperature setpoint (Security mode)
- display in Celsius or Fahrenheit

### ACCURACY

- accurate ambient temperature control of  $\pm 0.5$  °C (1 °F)
- CSA C828-13
- temperature sensing with thermistor

### TEMPERATURE RANGE

- 3 to 30 °C (37 to 86 °F)

### WARRANTY

- three years
- \* independent study
- † except STE403NP model

## TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	PACKAGING	UNIT PRICE
	CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES		
STE402NPWB+	150/260/300	2000/3475/4000	120/208/240	16.7	50/60	BOX	39.00
STE403NPW24	150/260/300/350/400	2000/3475/4000/4600/5750	120/208/240/277/347	16.7	50/60	BOX	106.00

Dimensions: 4 7/8 in. (124 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (29 mm) deep  
(STE403NP: 4 1/2 in. (114 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (35 mm) deep)

**STELPRO**

\*STELPRO reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products.  
For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).

