## **RWF | PULSAIR**<sup>™</sup> WALL FAN HEATER







## THE CLASSIC FAN HEATER

You won't find anything better than this efficient, durable and low noise fan heater. The Pulsair is extremely popular for many reasons. First, it can be recessed or surface mounted with a surface adapter (optional). It can also be mounted vertically or horizontally so that air can flow either up and down or right and left. Finally, the slim-line Pulsair can be recessed into a wall thickness of 2 in. to 3 in. While it's a winning heating solution for hallways or bathrooms, it can also be installed anywhere in the house, such as the office, or in commercial spaces. Its nichrome element provides instant heat. Available from 500 W to 2000 W, and from 120 V to 347 V, the Pulsair is recognized and recommended by those in the know.

### VERY QUIET FAN HEATER

#### THE MOST RESISTANT GRILLE **ON THE MARKET**

**INSTANT HEAT** NICHROME ELEMENT

MULTIPLE INSTALLATION OPTIONS

RECESSED. SURFACE MOUNTED. HORIZONTAL OR VERTICAL

#### ADAPTS TO MULTIPLE MARKETS

AVAILABLE IN: 120 V. 208 V. 240 V AND 347 V

#### **COLOURS**

- standard: white, soft white
- Orora (optional): refer to www.stelpro.com/en-CA/Orora

#### **FINISH**

• epoxy-polyester powdercoat

#### MANUFACTURING

- 20-gauge steel cabinet and 18-gauge steel grille
- quiet fan 40 CFM (500 W to 1000 W models) - 75 CFM (1250 W to 2000 W models)
- thermal protection with automatic reset

#### ELEMENT

• nichrome element produces instant heat

#### CONTROL

- built-in thermostat (optional)
- wall thermostat (not included) the use of an electronic thermostat is strongly recommended

#### **INSTALLATION**

- wall mounted
- recessed (wall must have a depth of 23/8 in. minimum)
- · surface mounted with surface adapter (optional)
- four installation positions

#### WARRANTY

· five years

## FOUR INSTALLATION OPTIONS





hallway, bathroom, locker room, office

# STELPRO


Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at www.stelpro.com.



TECHNICAL SPECIFICATIONS														
WITHOUT CONTROL		BUILT-IN THERMOSTAT		24 V CONTROL		POWER	VOLTAGE	FLOW		ROW ANCE	HEAT	RISE	WEIGHT	
CODE	PRICE	CODE	PRICE	CODE	PRICE	WATTS	VOLTS	CFM	М	FT.	°C	°F	KG	LB
RWF0501	164.00					500	120	40	2	6'6"	30	54	2.7	6
RWF0508	162.00					500	208	40	2	6'6"	30	54	2.7	6
RWF0502	162.00					500/375	240/208	40	2	6'6"	30	54	2.7	6
RWF0503	205.00	RWF0503T	237.00	RWF0503C24	254.00	500	347	40	2	6'6"	30	54	2.7	6
RWF0751	174.00					750	120	40	2	6'6"	67	121	2.7	6
RWF0758	170.00					750	208	40	2	6'6"	67	121	2.7	6
RWF0752	170.00					750/563	240/208	40	2	6'6"	67	121	2.7	6
RWF0753	213.00	RWF0753T	245.00	RWF0753C24	262.00	750	347	40	2	6'6"	67	121	2.7	6
RWF1001	176.00					1000	120	40	2	6'6"	76	136	2.7	6
RWF1008	173.00					1000	208	40	2	6'6"	76	136	2.7	6
RWF1002	173.00					1000/750	240/208	40	2	6'6"	76	136	2.7	6
RWF1003	216.00	RWF1003T	248.00	RWF1003C24	265.00	1000	347	40	2	6'6"	76	136	2.7	6
RWF1251	185.00					1250	120	75	2.1	6'10"	65	117	2.7	6
RWF1258	182.00					1250	208	75	2.1	6'10"	65	117	2.7	6
RWF1252	182.00					1250/938	240/208	75	2.1	6'10"	65	117	2.7	6
RWF1253	225.00	RWF1253T	257.00	RWF1253C24	274.00	1250	347	75	2.1	6'10"	65	117	2.7	6
RWF1501	189.00					1500	120	75	2.1	6'10"	79	141	2.7	6
RWF1508	185.00					1500	208	75	2.1	6'10"	79	141	2.7	6
RWF1502	185.00					1500/1125	240/208	75	2.1	6'10"	79	141	2.7	6
RWF1503	228.00	RWF1503T	260.00	RWF1503C24	277.00	1500	347	75	2.1	6'10"	79	141	2.7	6
						2000	120	75	2.1	6'10"	111	199	2.7	6
RWF2002	202.00					2000/1500	240/208	75	2.1	6'10"	111	199	2.7	6
RWF2008	202.00					2000	208	75	2.1	6'10"	111	199	2.7	6
RWF2003	245.00	RWF2003T	277.00	RWF2003C24	294.00	2000	347	75	2.1	6'10"	111	199	2.7	6

Add W for white or SW for soft white (consult the optional colours chart or contact your Stelpro representative for all other colours). Models also available in 277 V.

### **TECHNICAL DRAWINGS**



ACCESSORIES DESCRIPTION PRODUCT PRICE RWFT1\*\* built-in single pole thermostat [120 V-347 V]

30.00

42.00

43.00


RWFSA*	surface adapter

\* Add W for white or SW for soft white.

RWFT2\*

\* Supplied with a white knob (with a white grille) and a soft white knob (with a soft white grille)

built-in double pole thermostat [120 V-347 V]



Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at www.stelpro.com.