

# TG511A1000

## UNIVERSAL THERMOSTAT GUARD

### MANUFACTURING

- clear plastic
- compatible with all thermostats sold by Stelpro
- features a tumbler lock (keys included)
- can be installed without removing the thermostat from the wall

- protection against vandalism, damage and unauthorized tampering of settings

### WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
TG511A1000	UNIVERSAL THERMOSTAT GUARD	37.50

Inside dimensions: 6 1/16 in. x 5 1/16 in. x 2 15/16 in. (154 mm x 128.6 mm x 74.6 mm)



### KEYS (INCLUDED)

The ambient temperature can only be changed by the key owner.



# F29

## THERMOSTAT GUARD

### MANUFACTURING

- clear plastic (F290143) or metal (F290193)
- compatible with the STCNP, STCP, STE302R2+, STE241, T822K1034, T87K1015, D010 and ET180 thermostats
- features a tumbler lock (keys included)

- protection against vandalism, damage and unauthorized tampering of settings

### WARRANTY

- one year



F290143



F290193

PRODUCT	DESCRIPTION	PRICE
F290143	CLEAR PLASTIC THERMOSTAT GUARD	37.50
F290193	METAL THERMOSTAT GUARD	56.75

Inside dimensions: F290143: ring base of 3 1/2 in. x 6 3/8 in. x 3 1/4 in. (88.9 mm x 161.9 mm x 82.6 mm), solid base of 3 1/2 in. x 6 3/8 in. x 3 in. (88.9 mm x 161.9 mm x 76.2 mm)  
F290193: 3 13/16 in. x 6 in. x 3 1/8 in. (96.8 mm x 152.4 mm x 79.4 mm)



### KEYS (INCLUDED)

The ambient temperature can only be changed by the key owner.



# FD60M

## MECHANICAL TIMER

### COLOUR

- white

### VOLTAGE

- 20 A @ 120 Vac / 10 A @ 240 and 277 Vac

### INSTALLATION

- wall mounted with wall plate (not provided)

### CONTROL

- 60-minute timer
- used to control forced-air units such as: SK, RWF, SKS

### WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
FD60MCW70	60-MINUTE TIMER	67.25

Dimensions: 1.6 in. x 2.79 in. x 1.19 in. (40.6 mm x 70.9 mm x 30.2 mm)



# °STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).