

# STE402P

## ELECTRONIC THERMOSTAT – MULTIPLE PROGRAMMING

4000 W



### PROGRAMMING IS CHILD'S PLAY!

The STE402P multiple programming electronic thermostat takes care of everything, so you have peace of mind! This efficient unit lets you easily choose from 18 preset programs. With the touch of a button, the temperature setpoint will automatically change according to your selection.

**5-2** 5-2 DAY PROGRAMMING

**18** PREPROGRAMMING  
INCLUDES 18 PRESET PROGRAMS  
IN "PRE-PROG" MODE

**± 0.5°C** INCREASED SAVINGS AND COMFORT  
INCOMPARABLE ACCURACY

**ANTICIPATED START**  
REACH THE TEMPERATURE  
SETPOINT PRECISELY AT THE  
PROGRAMMED TIME

**BACKLIT SCREEN**  
CAN BE USED AS A NIGHTLIGHT

**ELECTRICITY SAVINGS**  
ENERGY SAVINGS OF 15-20%  
DEPENDING ON USE\*

#### COLOUR

- white

#### FINISH

- molded plastic

#### WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

#### CONTROL

- two- or four-wire connection
- compatible with forced-air units (Fan mode)
- easily choose the desired pre-programming with one button
- possibility of four events on weekdays and four events on weekends
- anticipated start (the thermostat reaches the desired temperature at the requested time)
- frost-free warning
- lock option at a minimum and maximum temperature setpoint (Security mode)

- protection against power failure (two hours)
- time displayed in 12- or 24-hour mode
- display in Celsius or Fahrenheit

#### ACCURACY

- accurate ambient temperature control of ± 0.5 °C (1 °F)
- CSA C828-13
- temperature sensing with thermistor

#### TEMPERATURE RANGE

- 3 to 30 °C (37 to 86 °F)

#### WARRANTY

- three years
- \* Independent study

### TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	PACKAGING	UNIT PRICE
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ		
STE402PWB+	150/260/300	2000/3475/4000	120/208/240	16.7	50/60	BOX	50.00

DIMENSIONS: 4 7/8 in. (124 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (29 mm) deep

**STELPRO**

\*STELPRO reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).



FC\_STE402P\_ENL\_031218