



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ITEM NO.	QTY. (PCS.)	PART NO.	DESCRIPTION
1	1	GMSCOM	PANDUIT SCREWDRIVER
2	1	PSL-KT	PSL-KT CARRYING CASE
3	6	PSL-BRD	Red Plastic body Padlock
4	1	PSL-1A	PSL-1A LOCKOUT HASP - 1.0" (25.4 mm) JAW DIAMETER
5	1	PSL-MLD	PSL-MLD MULTIPLE LOCKOUT DEVICE
6	3	PSL-WS	PSL-WS WALL SWITCH LOCKOUTS
7	3	PSL-CBNT	NO TOOL CIRCUIT BREAKER LOCKOUT
8	3	PSL-P	PSL-P PLUG LOCKOUTS
9	15	PVT-98	PVT-98 "EQUIPMENT LOCKED OUT BY.." SAFETY TAGS
10	15	PLT25	NYLON CABLE TIES
11	1	GMPSL-INMLD	INSTRUCTION SHEET
12	1	GMPSL-INI	INSTRUCTION SHEET



PSL-KT
PLASTIC CARRYING CASE

CAD FILENAME/LAYERS: 100619CW-DC-C10386/03D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PSL-KT-CONA
LOCKOUT KIT CONTRACTOR

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

SCALE: NTS

DRAWN BY: RVU
DATE: 10-18-05
CHK'D: / /

DRAWING NO.: C10386
DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	11/17/09	RVU		PSL-8 WAS PSL-3RED-LS, ADD LEADERS 12 AND 13 FOR GMPSL-INMLD, AND PSL-INI. REMOVED PSL-PLIREDY and PSL-3RED.	5905	R		
2	02-04-08	JHAC		REMOVED GSLLOCKOUT, CHANGED PSL-CB TO PSL-CBNT, AND ADDED PSL-PLIREDY	5279	R		
1	12-10-07	JHAC		PSL-3RED-LS WAS PSL-5RED-LS AND PSL-3RED WAS PSL-5RED	5230	R		
0	10-18-05	RVU		DRAWING RELEASE	4258	R		