



PORTABLE IN-LINE 15A GFCI OUTLET ADAPTER, MANUAL RESET

1594PC2M | [Pass & Seymour](#)



FEATURES & BENEFITS

Portable Ground Fault Circuit Interrupter, 2' Cord 15amp 125volt, Manual Reset

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Durable polycarbonate case withstands hard use.
- In-line has bright, green power indicator light that is on when power is available and is visible from both sides of the GFCI.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: In-Line Portable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: Yes

CSA Standard: C22.2 No. 42, 144

CUL Listing No: E42190

cULus: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121614

DIMENSIONS

Length (US): 27.75"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15P/R
NEMA Rating: Yes
Volts: 125V
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No