



PLUGTAIL® HOSPITAL-GRADE 15A SELF-TEST GFCI RECEPTACLE, RED

PT1597HGRED | [Pass & Seymour](#)

FEATURES & BENEFITS

The fastest-installing GFCI ever now conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements: survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- For Self-Test GFCI FAQ, [click here](#).

SPECIFICATIONS

GENERAL INFO

Color: Red

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CSA Listed: No
cULus: Yes
Federal Spec: Yes
UL Standard: UL498

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA