

## T120R0PPH4



Article Number: 111-12066

Heavy Duty Cable Tie, 15.2" Long, 60lb Tensile Strength, PP, Black, 500/pkg



### Base Data

Local Order Number T120R0PPH4

Type T120R

Color Black (BK)

- Features and Benefits**
- Polypropylene cable ties provide excellent resistance to chemicals and salts.
  - Head design provides high tensile strength with very low insertion force.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure plastic pawl

Variant Inside Serrated

Short Description Heavy Duty Cable Tie, 15.2" Long, 60lb Tensile Strength, PP, Black, 500/pkg

### Product Dimensions

Minimum Tensile Strength (imperial) 60.0 lbs

Minimum Tensile Strength (N) 267.0 N

Length L (imperial) 15.35 "

Length L (metric) 390.0 mm

Width W (imperial) 0.3 "

Width W (metric) 7.6 mm

Bundle Diameter min (imperial) 0.5 "

Bundle Diameter min (metric) 12.7 mm

Bundle Diameter max (imperial) 4.1 "

Bundle Diameter max (metric) 105.0 mm

Thickness T (imperial) 0.07 "

Thickness T (Metric) 1.8 mm

### Logistics and Packaging

Quantity per bag

Package Quantity 500

Carton Quantity 1000 Pieces

Weight (Metric) 5.2 kg

## Material and Specifications

---

<b>Material</b>	Polypropylene (PP)
<b>Material Shortcut</b>	PP
<b>Flammability</b>	UL94 HB
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40 °F to +239 °F (-40 °C to +115 °C)
<b>ROHS Conformity</b>	Yes