

MCB-01

General Information

| | |
|-------------------------------|-----------------------|
| Extended Product Type: | MCB-01 |
| Product ID: | 1SFA611610R1010 |
| EAN: | 7320500307762 |
| Catalog Description: | MCB-01 Contact block |
| Long Description: | Modular contact block |



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights Accessories

Parts & Services » Robotics » Application Equipment & Accessories » Arc Welding Equipment

SparePartUsedOnList

Ordering

| | |
|--------------------------------|---------------|
| EAN: | 7320500307762 |
| Minimum Order Quantity: | 10 piece |
| Customs Tariff Number: | 85369001 |

Dimensions

| | |
|----------------------------|---------|
| Product Net Width: | 0.044 m |
| Product Net Height: | 0.010 m |
| Product Net Depth: | 0.028 m |
| Product Net Weight: | 0.04 kg |

Container Information

| | |
|--------------------------------------|----------|
| Package Level 1 Units: | 10 piece |
| Package Level 1 Width: | 0.11 m |
| Package Level 1 Height: | 0.01 m |
| Package Level 1 Length: | 0.15 m |
| Package Level 1 Gross Weight: | 0.04 kg |

Environmental

| | |
|---------------------|---|
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|---------------------|---|

Additional Information

| | |
|------------------------------|---|
| Accessory Type: | Contact blocks and holders |
| Block: | Single contact block |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 |
| Function: | Without holder |

| | |
|---|--|
| IIT Publishing Status: | Level 0 - Information enabled |
| Illumination: | Non-illuminated |
| Mechanical Durability: | 10 million |
| Number of Auxiliary Contacts NC: | 1 |
| Product Main Type: | MCB |
| Product Name: | Contact block |
| Product Range: | Modular range |
| Product Type: | MCB |
| Rated Frequency (f): | Supply Circuit 50 Hz Supply Circuit 60 Hz |
| Rated Operational Current AC-15 (I_e): | (220 / 240V) 6 A (24 / 127V) 8 A |
| Rated Operational Current DC-13 (I_e): | (125V) 1.1 A (24V) 5 A |
| RoHS Date: | 0635 4 |
| Technical Information: | CONTACT |

Certificates and Declarations (Document Number)

| | |
|--|-----------------|
| Declaration of Conformity - CE: | 1SFA1-83 |
| RoHS Information: | 1SFC151011D0203 |

Classifications

| | |
|------------------------------------|--|
| E-nummer: | 3714006 |
| ETIM 4.0: | EC002024 - Accessories for control circuit devices |
| ETIM 5.0: | EC002024 - Accessories for control circuit devices |
| Object Classification Code: | S |
| UNSPSC: | 39121500 |
