


M2SS2-31G

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	M2SS2-31G
Product ID:	1SFA611201R3102
EAN:	7320500285176
Catalog Description:	M2SS2-31G Selector Switch
Long Description:	Modular Selector Switch - 2-Pos Maintained - Short handle - Green - Illuminated - Chrome metal - No contact block



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot
Devices » Operator and Pilot Lights

Ordering

EAN:	7320500285176
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.048 m
Product Net Height:	0.030 m
Product Net Depth:	0.050 m
Product Net Weight:	0.034 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.03 m
Package Level 1 Length:	0.15 m
Package Level 1 Gross Weight:	0.034 kg

Environmental

Ambient Air Temperature:	Operation -25 ... +70 °C Storage -30 ... +85 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Actuator Type:	Short handle
Bezel Material:	Chrome metal
Block:	No contact block
Color:	Green
Function:	Maintained
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Illuminated
Maintained Positions:	A, C
Mechanical Durability:	0.5 million

Product Main Type:	M2SS2
Product Name:	Selector Switch
Product Range:	Modular
Product Type:	M2SS
RoHS Date:	0635 4
Sub-Function:	2-position

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-83
RoHS Information:	1SFC151011D0203

Classifications

E-nummer:	3715912
ETIM 4.0:	EC002024 - Accessories for control circuit devices
ETIM 5.0:	EC002024 - Accessories for control circuit devices
Object Classification Code:	S
UNSPSC:	39121500
