

MCB-10G

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	MCB-10G
Product ID:	1SFA611610R1101
EAN:	7320500307793
Catalog Description:	MCB-10G Contact block
Long Description:	Modular contact block



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights
Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights Accessories

Ordering

EAN:	7320500307793
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.044 m
Product Net Height:	0.010 m
Product Net Depth:	0.028 m
Product Net Weight:	0.04 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.01 m
Package Level 1 Length:	0.15 m
Package Level 1 Gross Weight:	0.04 kg

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Additional Information

Accessory Type:	Contact blocks and holders
Block:	Gold plated contact block
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Function:	Without holder
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Non-illuminated
Mechanical Durability:	10 million
Number of Auxiliary Contacts NO:	1
Product Main Type:	MCB
Product Name:	Contact block
Product Range:	Modular range

Product Type: MCB
Rated Frequency (f): Supply Circuit 50 Hz
Supply Circuit 60 Hz
Rated Operational Current AC-15 (I_e): (220 / 240V) 6 A
(24 / 127V) 8 A
Rated Operational Current DC-13 (I_e): (125V) 1.1 A
(24V) 5 A
RoHS Date: 0635 4

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SFA1-83
RoHS Information: 1SFC151011D0203

Classifications

E-nummer: 3714007
ETIM 4.0: EC002024 - Accessories for control circuit devices
ETIM 5.0: EC002024 - Accessories for control circuit devices
Object Classification Code: S
UNSPSC: 39121500
