

OS30FAJ12

ABB contact for Canada [Print to Pdf..](#)

General Information

Extended Product Type:	OS30FAJ12
Product ID:	1SCA108824R1001
EAN:	6417019420919
Catalog Description:	OS30FAJ12 Switch fuse
Long Description:	Switch fuse 30A. Front operated,3-pole,for UL fuse type,sizes J, 30A. Handle and shaft has to be ordered separately.



Categories

Products » Low Voltage Products and Systems » Switches » Switch Fuses

Ordering

EAN:	6417019420919
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Dimensions

Product Net Width:	143 mm
Product Net Height:	100 mm
Product Net Depth:	119 mm
Product Net Weight:	0.7 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	240 mm
Package Level 1 Height:	130 mm
Package Level 1 Length:	108 mm
Package Level 1 Gross Weight:	0.7 kg
Package Level 1 EAN:	6417019420919

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-05-01
---------------------	--

Technical UL/CSA

Ampere Rating UL/CSA:	30 A
Horse Power Rating UL/CSA:	acc. to UL 208V 7.5 Hp acc. to UL 480V 15 Hp acc. to UL 600V 20 Hp

Additional Information

Fuse Size:	J, 30A
Fuse Type:	UL

Handle Type:	Not included
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Normal
Number of Poles:	3
Operating Mechanism:	Mechanism between the poles
Operating Mode:	Front Operated
Position of Line Terminals:	Top in - bottom out
Product Main Type:	OS32
Product Name:	Switch fuse
Rated Operational Voltage:	690 V AC
Standards:	UL
Terminal Type:	Screw Terminals

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SCC311010D0201
RoHS Information:	1SCC311106D0201

Classifications

ETIM 5.0:	EC001040 - Fuse switch disconnecter
Object Classification Code:	Q
