

M3SS7-10B

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	M3SS7-10B
Product ID:	1SFA611216R1006
EAN:	7320500300589
Catalog Description:	M3SS7-10B Selector Switch
Long Description:	Modular Selector Switch - 3-Pos Maintained/Momentary, B and C fixed, spring return from A to B - Short handle - Black - Non-illuminated - Black plastic - No contact block



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot
Devices » Operator and Pilot Lights

Ordering

EAN:	7320500300589
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.048 m
Product Net Height:	0.030 m
Product Net Depth:	0.050 m
Product Net Weight:	0.019 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.03 m
Package Level 1 Length:	0.15 m
Package Level 1 Gross Weight:	0.019 kg

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Additional Information

Actuator Type:	Short handle
Bezel Material:	Black plastic
Block:	No contact block
Color:	Black
Function:	Maintained/Momentary
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Non-illuminated
Maintained Positions:	B, C
Mechanical Durability:	0.5 million
Product Main Type:	M3SS7

Product Name:	Selector Switch
Product Range:	Modular
Product Type:	M3SS
RoHS Date:	0635 4
Spring Return From:	A to B
Sub-Function:	3-position

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-83
RoHS Information:	1SFC151011D0203

Classifications

E-nummer:	3715745
ETIM 4.0:	EC002024 - Accessories for control circuit devices
ETIM 5.0:	EC002024 - Accessories for control circuit devices
Object Classification Code:	S
UNSPSC:	39121500
