

RB121A-115VAC/DC

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	RB121A-115VAC/DC
Product ID:	1SNA645007R0100
EAN:	4013614507786
Catalog Description:	RB121A-115VAC/DC Interface relay R600 1c/o,A1-A2=115VAC/DC,250V/1mA- 6A,LED
Long Description:	Screw relay RB121A 115vac/dc : 115vac- dc input / 1SPDT 1 mA upto 6A with led



Categories

Products » Low Voltage Products and Systems » Control Products »
Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

EAN:	4013614507786
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900

Dimensions

Product Net Width:	6 mm
Product Net Height:	67.5 mm
Product Net Depth:	70 mm
Product Net Weight:	0.02 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	3472596450076

Technical

Function:	Boxed interface relay R600
Sub-Function:	Relay with built in LED
Output:	1 c/o (SPDT) contact
Output Signal:	5 ... 250 V AC / 1 mA ... 6 A
Rated Control Supply Voltage (U_s):	115 V AC/DC
Terminal Type:	Screw Terminals

Certificates and Declarations (Document Number)

CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Declaration of Conformity - CE:	1SND225042C1000
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
LR Certificate:	LRS_0620042

UR Certificate: UR_E352056

Classifications

Object Classification Code:	K
ETIM 4.0:	EC001437 - Switching relay
ETIM 5.0:	EC001437 - Switching relay
UNSPSC:	39121500
eClass:	7.0 27371601
