
LIGHTOLIER

by (s) ignify

Downlighting

LytePoints 3 3/4"

302MRSPX Non-IC Frame MR16



Complete fixture consists of Reflector Trim & Remodeler. Select each separately.

Frame-in Kit	Opening	Reflector Trim
302MRSPX	3-3/4 (95mm)	Accepts all 3-3/4 (95mm) 300X Series trims; See Reflector Trim specification sheets.

Features

- 1. Mounting Frame: No.20 ga. (.032") galvanized steel. Four slots are positioned 90° apart to simplify alignment of luminaires.
- 2. Mounting Bars: 20ga. galvanized steel. Lockable on frame-in kit. Extend from 14" (356mm) to 25" (635mm). Pre-installed integral nails for secure attachment to wood joists. Attaches to T-bar ceilings without the need of accessories.
- Socket: Porcelain body; Two-pin (GX5.3 base). Pre-wired with 18 ga. Teflon 250° leads to junction box. Replacement part number SK9070C.
- 4. Socket Cup: .022" galvanized steel. Easy snap-on to housing.
- 5. Junction Box: 4" (102mm) x 3" (76mm) x 2" (51mm) 18 ga. galvanized steel. CSA certified for maximum of 8 No. 23 ga., 90° C through branch circuit. conductors. Integral cable clamp permit attachment of non metallic cable without need of additional connectors. Pry-out knock-outs accept BX cable. Easy access from both sides with snap on covers.
- Potted Transformer: 50VA Magnetic, 120 volts primary, nominal 12 volt secondary, class "H". Can be removed easily. Fully encapsulated in epoxy resin inside aluminum casing.
- Thermal Protector: Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from mounting frame sides and junction box.

Dimming

Dimming controls: Use only dimmers specifically designed for use with magnetic transformers, like Lightolier Onset series, Sunrise series LV or VA dimmers, or any Lightolier Controls dimming system.

Labels

CSA, UL

Rated for Damp or Wet location depending on trim used.



© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855–486–2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008