



PLUG-IN RF TRU UNIVERSAL LAMP MODULE

LC2150 | [On-Q](#)

FEATURES & BENEFITS

Control all dimmable table and floor lamps (up to 300W) with this plug in RF module. Can be linked to and operated by other RFLC devices and controllers, and plugs into any grounded outlet.

radiant® Screwless Wall Plate not included.

Check out the [RF Lighting Control mobile app](#).

- Operates all dimmable lighting types and loads (up to 300W) via the [mobile app](#)
- Easy-to-install using the home's existing grounded electrical 120V outlets
- Integrates with Legrand's [intuity](#) and [third party](#) home automation systems
- Fully compatible with the [radiant®](#) RF Lighting Control and [adore®](#) Wi-Fi Ready lighting control devices

SPECIFICATIONS

GENERAL INFO

Size: Unit Package: 2.48"h x 3.03"w x 4.8"d, Master Carton: 9.8"h x 6.7"w x 13.78"d

Special Features: lamp module, remote, Intuity Home Intelligence

DIMENSIONS

Height (Metric): 90.98mm

Height (US): 3.582"

Length (Metric): 50.29mm

Length (US): 1.98"

Width (Metric): 58.72mm

Width (US): 2.312"

Weight: 0.38 lbs

TECHNICAL INFORMATION

AC Voltage Input: 120V 60Hz

Frequency: Frequency Rating: 900 MHz

Humidity: Up to 90% Relative Humidity (non-condensing)

Load: Max 300W-incandescent, 300W-ELV, 200W-CFL, 200W-LED

Mounting: Plugs into a standard electrical wall outlet
Operating Temperature (Celsius): 0° ~ 40°C