
12VDC, 18W POWER SUPPLY

PW7760 | [On-Q](#)



FEATURES & BENEFITS

Powers connected home devices by converting high voltage alternating current (AC) to low voltage direct current (DC)



- Package includes a DC power supply with 2 ft barrel connector plug and a 1.5 ft AC power plug
- IEC C7/C8 connections ("figure 8")
- Stacks neatly in enclosure with AC1031 power strip

SPECIFICATIONS

GENERAL INFO

Type: Power Supply

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
FCC Standard: Yes
UN SPSC: 39121006

DIMENSIONS

Height (Metric): 3.3 cm
Height (US): 1.3"
Length (Metric): 8 cm
Length (US): 3.15"
Width (Metric): 5 cm
Width (US): 1.97 in

TECHNICAL INFORMATION

AC Voltage Input: 100-240VAC

Efficiency: 0.7650000000000001

Humidity: Max Noncondensing 85%

mA: 1500 mA

Mounting: Desktop

Operating Temperature (Celsius): 0°C to 40°C

Storage Temperature: -20°C to 60°C

Volts (DC): 12 VDC

Watts: 18 W

Receptacle Type: DC Barrel Jack

Number Of Receptacles: 1