



# **Standard**

# STANDARD MAG BALLAST (2) 26W COMPACT(2-PIN) 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

#### **Product data**

General Information			
Lamp Type	CFQ26W/G24D		
Number of Lamps	2 piece/unit		
Lamp Footage	-		
Ballast Type	Magnetic Fluorescent		
Base Model	H2Q26TPBLS		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical			
Input Voltage	120 V		
Input Frequency	60 Hz		
Total Harmonic Distortion USA	15 %		
Ignition Method	Preheat		
Crestfactor (Nom)	1.7		
Ignition Time (Nom)	1s		
Input Current (Open Circuit)	0		
Ballast Factor (Nom)	0.9		
Power Factor (Nom)	0.98		
Input Current (Nom)	0.44 A		
Input Power (Nom)	52 W		
Rated Lamp Power	26 W		

Wiring			
Wire Striplength	0.50/0.375 mm		
Lamp Connection	Series		
Wire Length by Color	See data sheet		
Wire Gauge (Nom)	18AWG mm		
Wire Type	Solid		
Remote Wiring Configuration Allowed	Yes		
Tandem Wiring Configuration Allowed	Yes		
Through Wiring Configuration Allowed	Yes		
Max Ballast-Lamp Distance Remote Wiring	30'		
Max Ballast-Lamp Distance Tandem Wiring Any = 30'			
Max Ballast-Lamp Distance Through Wiring Any = 30'			
Mechanical and Housing			
Housing Material	Metal		
Housing	R5		
Housing Dimensions	9.5" x 2.38" x 1.69"		
Approval and Application			
EMC Immunity Standard	FCC Non-Consumer		
Approval Marks	CSA certificate UL certificate RoHS		
	Compliant		
Hum And Noise Level	A		


Datasheet, 2019, March 22 data subject to change

## **Standard**

UL Recognized	No		
Product Data			
Order product name	STANDARD MAG BALLAST (2) 26W		
	COMPACT(2-PIN) 120V		
EAN/UPC - Product	781087061558		
Order code	913700589709		

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913700589709
Net Weight (Piece)	1.611 kg

### Dimensional drawing



MAG BALLAST (2) 26W COMPACT(2-PIN) 120V

Product	A1	A2	B1	C1
STANDARD MAG BALLAST (2) 26W	9.5 in	8.91 in	2.38 in	1.69 in
COMPACT(2-PIN) 120V				



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.