


## 









NOTES:

- 1. FOR NICKEL PLTE PER QQ-N-290, CLASS 2, TYPE IV, ADD SUFFIX 'NP" TO CATALOG NO. EXAMPLE: AA2NP
- 2. CAT. NOS. AA2, BB2, & NO. 675-51973 COMPLY WITH BU SHIPS SPEC MIL-T-16366, TYPE CCBC.
- 3. FOR SILVER PLTE, ADD SUFFIX "SP" TO CAT. NO. EXAMPLE: BB2SP FOR #675-51973 SILVER PLTE ORDER #675-51973-1

MATERIAL: COPPER FINISH: ELECTRO-TIN PLTE (SEE NOTES)

## \*STRANDED AND SOLID FOR 22-10 AWG COPPER WIRE STRANDED FOR 9-1 AWG COPPER WIRE

CAT.	DIST.	FIG.	WIRE SIZE		±.015	±.010		INSTALLING TOOLS			
NO.	CAT. NO.		AWG*	NAVY	<b>A</b>	<b>B</b>	MARKING		FIXED DIE TOOLS	TBM6 TBM65 WITH DIES	
AA2	2A-18	1	22-16	1-2	.63	.13	A 22-16	WT110M,WT111M WT112M, ERG2002, ERG2005(B&C ONLY) WT1300, WT2000	-	-	
BB2	2B-14	1	18–14	2-1/2 - 4	.63	.16	B 14-18				
CC2-TB	2C-10	1	12-10	-	.71	.22	C 10-12				
675-51973	. <del></del>	1	12-9	6-9	.81	.23	NAVY 6-9	WT3155A(B&C ONLY)			
DD102	2D-8	З	8-10	-	.99	.27	DD102	WT3155A		11803 NEST 11802 INDENTOR 11805 NEST 11802 INDENTOR 11806 NEST 11802 INDENTOR	
EE2	2E-6	З	6	-	1.12	.307	EE-2				
FF2	2F-4	З	4-3		1.12	.377	FF-2	-			
GG2	2G21	2	2-1	-	1.72	.47	GG-2				

GENERAL NOTES				Thomas&Betts					
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.	www.tnb.com			A Member of the ABB Group					
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.	DESCRIPTION: STA-KON								
REVISIONS	NON-INSULATED BUTT SPLICE								
** 000000000000000000000000000000000000	NON-INSOLATED BOTT SPEICE								
SEE ERN (**** ) FOR APPROVAL SIGNATURES	ORIGINAL PROJECT NO / ( ERN NO )	SHEET NO:	REV. NO:	DRAWING NO:					
& RELEASE DATE. PROJECT NO: ****	TM400023 / ( 2016425)	1 OF 1	0	WSD-001494					

THIS DRAWING IS INTENDED FOR DESCRIPTIVE PURPOSES ONLY. AND THE RIGHT IS RESERVED TO DEVIATE FROM ANY OF THE DETAILS SHOWN HEREON. COPYRIGHT THOMAS & BETTS CORPORATION. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL.