







ALL DIMENSIONS ARE APPROXIMATE. FOR REFERENCE ONLY.

NOTES:

- (I). TERMINAL: HIGH CONDUCTIVITY COPPER.
- (2). FINISH: ELECTRO TIN PLATE
- (3). INSULATOR: NYLON, TRANSLUCENT.
 (4). CERTIFIED FOR 600V, 1000V IN SIGNS & FIXTURES
 (5). RATED FOR 105° MAX. TEMPERATURE

FOR CUSTUM CONNECTORS:

PLATING:

NP-NICKLE PLATED, SP-SILVER PLATED, LP-LEAD PLATED, PF-PLAIN FINISH

BENT TONGUES:

UF-45 DEGREE and UB-90 DEGREES

BOLT HOLES:

02-#8, 03-#10, 04-1/4", 05-5/16", 06-3/8", 08-1/2", 10-5/8"

BOLT HOLE SPACING:

08-1/2", 09-9/16", 10-5/8", 11-11/16" etc up to 28-1-3/4"

STACKING:

T-TOP and B-BOTTOM

INSPECTION HOLE:

PH-PEEP HOLE or BE-BLIND END

TONGUE WIDTH

NT - NARROW TONGUE

GENERAL NOTES			_	
I. ALL DIMENSIONS ARE FOR REFERENCE ONLY.				homas@Betts
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.	DESCRIPTION: Colo	r Vound	· INICIII A	
REVISIONS		r-Keyed		TED CONNECTORS,
	WIRE SIZES	*8-250 I	MCM - CO	LOR CODE
SEE ERN (2012575) FOR APPROVAL SIGNATURES	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
& RELEASE DATE.03/16/11 PROJECT NO: CD55874	CD55874 / (2010390)	1 OF 3	1	WSD-000451

Cat No.	Bolt	А	В	С	D	E	TBM6S or 25000 Tool	Hydraulic 13642M
541041	#10	1.49	. 50	. 39	. 08	. 34	11821-CK	21707M-CK
541051	1 / 4	1.58	. 53	. 44	. 07	. 42	11822-CK	21708M-CK
541061	1/4	1.80	. 60	. 55	. 09	. 51	11823-CK	21709M-CK
541081	1/4	2.06	. 65	. 68	. 11	. 58	11824-CK	21710M-CK
541091	3/8	2.37	. 93	. 75	. 13	. 62	11825-CK	21711M-CK
541101	3/8	2.43	. 93	. 83	. 13	. 67	11826-CK	21712M-CK
541111	3/8	2.55	. 93	. 92	. 13	. 76	11827-CK	21713M-CK
541121	3/8	2.76	. 93	1.03	. 4	. 78	11828-CK	21714M-CK
541131	1/2	3.20	1.25	1.13	. 4	. 86	11829-CK	21715M-CK

			T	nomas@Betts www.tnb.com
DESCRIPTION:	Colo: Wire size	*-Keyed S #8-250	INSUL/ MCM - CO	ATED CONNECTORS, OLOR CODE
		SHEET NO: 2 OF 3	REV. NO:	DRAWING NO:

Cat No.	Bolt	А	В	С	D	E	G	TBM6S or 25000 Tool	Hydraulic 13642M
542041	#10	2.20	1.18	. 42	. 08	. 34	.625	11821-CK	21707M-CK
542051	1/4	2.32	1.28	. 44	. 08	. 42	. 625	11822-CK	21708M-CK
542061	1/4	2.40	1.28	. 52	. 10	. 51	. 625	11823-CK	21709M-CK
542081	1/4	2.69	1.28	. 68	. 11	. 58	. 625	11824-CK	21710M-CK
542091	3/8	3.36	1.93	. 75	. 13	. 62	1.00	11825-CK	21711M-CK
542101	3/8	3.43	1.93	. 83	. 13	. 67	1.00	11826-CK	21712M-CK
542111	3/8	3.46	1.81	. 94	. 4	. 76	1.00	11827-CK	21713M-CK
542121	3/8	3.75	1.93	1.03	. 4	. 78	1.00	11828-CK	21714M-CK
542131	1/2	3.87	1.93	1.13	. 4	. 86	1.00	11829-CK	21715M-CK

SAME AS SHEET ONE EXCEPT TWO HOLES

			7	homas@Betts www.inb.com			
DESCRIPTION:	Color-Keyed insulated connectors,						
WIRE	SIZES	#8-250 N	<u> 1CM - C</u>	OLOR CODED			
		SHEET NO:	REV. NO:	DRAWING NO:			
		3 OF 3		WSD-000451			