



U39RT

by Burndy
Catalog ID: U39RT

Prop 65 Notice

Stainless Steel Circular Non-Butting Twin Die, U die, 750 Kcmil/600 Flex, Black, Index 24

Die Index: 24

Product Details

General

| | |
|------------------------------|--|
| Application | Crimping |
| Application - For Use On | Fit in Y35, Y39, Y750, PAT 750 Tools Series; Fit in Y46 (with PUADP-1 Adapter), PAT46 Tools series; Fit in Y45 (With PT6515 Adapter) |
| Color Code | Black |
| Construction Material - Main | Stainless Steel |
| Crimp Force Capacity | 12 ton |
| Die Index | 24 |
| Die Type | U DIE |
| Material | Stainless Steel |
| Sub Brand | U-DIE |
| UPC | 781810627433 |
| UPC 12 Digit | 7818106274333 |

Dimensions

| | |
|------------------------|---------|
| Dimension - Width inch | 1.38 |
| Dimension - Width mm | 35 |
| Weight | 0.26 lb |

Conductor Related

| | |
|-----------------|--------------------|
| Crimping Ranges | 750 Kcmil/600 Flex |
|-----------------|--------------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|--------------|
| Minimum Pack Quantity | 1 |
| Package Contents | Die set only |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)