



# **T&B' Fittings**







### NOTES:

ALL DIMENSIONS REFERENCE ONLY ١.

DIMENSION "A" IS WITH GLAND THREADED FULLY TO SHOULDER.


3. MATERIAL: IRON

FINISH: ZINC PLATED 4.

ALL CONNECTORS PROVIDED WITH FULL PERIMETER SLEEVE INSULATED THROAT.







3743-TB	l" (27)	2.750 (69.85)	.700 (17.78)	1.755 (44.58)
3742	3/4" (21)	2.375 (60.33)	.700 (17.78)	1.500 (37.50)
3741	1/2" (16)	1.950 (49.53)	.600 (15)	1.250 (31.75)
3740	3/8" (12)	1.950 (49.53)	.600 (15)	1.250 (31.75)
CAT#	SIZE	DIM A	DIM B	DIM C

#### **GENERAL NOTES**

ALL DIMENSIONS ARE FOR

REFERENCE ONLY.
DIMENSIONS IN BRACKETS [ ]
ARE IN METRIC UNITS.

#### REVISIONS

SEE ERN ( \*\*\*\* ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: \*\*\*\* DESCRIPTION:

## LIQUID TIGHT CONNECTOR FOR TYPE A CONDUIT

ORIGINAL PROJECT NO / ( ERN NO )

SHEET NO:

REV. NO:

DRAWING NO:

Thomas@Betts

WSD-000108 RD52305 / ( 2005182) 1 OF 1