

Rigid Conduit

Bushings



**CIRB6R4 /
CIRB16R12**



BU-201 / BU-210



CI2404 / CI2440



CI2704 / CI2748




Rated 105°C

Cat. No.	Trade Size (in.)
Reducing Bushings - NPS (Steel)	
CIRB6R4	3/4 x 1/2
CIRB8R4	1 x 1/2
CIRB8R6	1 x 3/4
CIRB10R4	1-1/4 x 1/2
CIRB10R6	1-1/4 x 3/4
CIRB10R8	1-1/4 x 1
CIRB12R4	1-1/2 x 1/2
CIRB12R6	1-1/2 x 3/4
CIRB12R8	1-1/2 x 1
CIRB12R10	1-1/2 x 1-1/4
CIRB16R4	2 x 1/2
CIRB16R6	2 x 3/4
CIRB16R8	2 x 1
CIRB16R10	2 x 1-1/4
CIRB16R12	2 x 1-1/2
Conduit Bushings (Zinc Die Cast)	
BU-201	1/2
BU-202	3/4
BU-203	1
BU-204	1-1/4
BU-205	1-1/2
BU-206	2
BU-207	2-1/2
BU-208	3
BU-209	3-1/2
BU-210	4

Cat. No.	Trade Size (in.)
Insulated Metallic Bushings (Aluminum)	
CI2404*	1/2
CI2406*	3/4
CI2408	1
CI2410	1-1/4
CI2412	1-1/2
CI2416	2
CI2420	2-1/2
CI2424	3
CI2428	3-1/2
CI2432	4
CI2440	5
Plastic Bushings	
CI2704	1/2
CI2706	3/4
CI2708	1
CI2710	1-1/4
CI2712	1-1/2
CI2716	2
CI2720	2-1/2
CI2724	3
CI2728	3-1/2
CI2732	4
CI2740	5
CI2748	6

* Models CI2404 & CI2406 are in zinc

CI2604 / CI2632



With solid copper lug

Cat. No.	Trade Size (in.)	Ground Wire Size (AWG)
Insulated Grounding Bushings (Aluminum)		
CI2604	1/2	14-6
CI2606	3/4	
CI2608	1	
CI2610	1-1/4	14-4
CI2612	1-1/2	
CI2616	2	6-1/0
CI2620	2-1/2	
CI2624	3	2-4/0
CI2628	3-1/2	
CI2632	4	

