
Wallplates and accessories | Designer | Claro and Satin Colors



Product family features

- Can be used in conjunction with the following dimmer(s), switch(es), sensor(s), and accessories: Maestro®, Maestro IR®, Maestro Wireless®, Caséta® Wireless, Pico® wireless, Diva®, Skylark Contour® and Skylark® controls, and Claro® and Satin Colors® accessories
- · All Lutron wallplates are screwless, seamless, and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- · Full line of wiring devices in Designer style opening
- · Blank inserts available for Gloss (DV-BI-) and Satin Colors (SC-BI-)
- · Customize your designer wallplate with engraving. Contact customer service to get started; 1.888.LUTRON1

Ganging and derating


- · Designer wallplates use standard ganging
- · Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see p. 246
- · May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, see pp. 250-252

Available finishes

Use ${f BOLD}$ color code in model number (Example: SC-1- ${f PL}$)

Gloss finishes





^{*}Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

GFCI Receptacles



- Self-testing technology allows GFCI to automatically check proper operation every 30 seconds
- LEDs indicate status of GFCI protection function
- Press reset button to reset GFCI after circuit interruption
- Wallplate sold separately

Tamper-resistant, self-testing GFCI receptacles

15A 12	5V, GFCI	CAR-15-GFST-XX1
15A 12	5V, GFCI	SCR-15-GFST-XX2
20A 12	5V, GFCI	SCR-20-GFST-XX2

Receptacles for dimming use



- Duplex for dimming both connected loads
- · Projecting nubs prevent standard plugs from being used
- · Requires replacement plug for dimming table and floor lamps
- Tamper resistant shutter mechanism

Dual dimming, tamper-resistant receptacles

15A 120/125V SCR-15-DDTR-X	15A 1	120/125 V	CAR-15-DDTR-XX1
	15A 1	120/125V	SCR-15-DDTR-XX ²
20A 120/125V CAR-20-DDTR-X	20A 1	120/125V	CAR-20-DDTR-XX1
20 A 120/125 V SCR-20-DDTR-X	20A 1	120/125V	SCR-20-DDTR-XX2

XX1: Gloss color codes, see p. 235 XX²: Satin Colors® codes, see p. 235

Receptacles for half dimming use



- Top half for dimming
- · Projecting nub prevents standard plug from being used
- · Requires replacement plug for dimming table and floor lamps
- · Bottom half is a general use receptacle and will fit standard duplex plugs
- Tamper resistant shutter mechanism

Half dimming, tamper-resistant receptacles

15A 120/125V	CAR-15-HDTR-XX1
15A 120/125V	SCR-15-HDTR-XX ²
20A 120/125V	CAR-20-HDTR-XX1
20A 120/125V	SCR-20-HDTR-XX ²