
Accessories

Wallplates

4.75 in (121 mm)



Coordinated electrical devices



For more information about coordinated Designer electrical devices, see p.237.



Shown actual size: Diva preset dimmer and 1-gang Claro wallplate in White (WH).

Product family features

- Large paddle switch with a captive linear-slide dimmer for a standard designer wallplate opening
- Preset dimmer
- Select lighter color models feature built-in soft-glow locator light*
- · C·L® and eco-dim® models available
- Coordinating Claro_®, Satin Colors_®, and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates; see p. 237

Control types

Single-pole (one location)

0 0 0 3-way or 4-way (two or more locations)

Direct load type compatibility

Incandescent/halogen lighting

- ♥/♥ Dimmable CFL/LED lighting (screw-base)
- Electronic low-voltage lighting
- Z = Fluorescent lighting
- LED lighting
- Switched lighting/fan/motor
- S Ceiling fans

Load type requiring load interface

Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage, and capacity combinations.

For additional information, see pp. 255-259.

* Locator light not available in C·L and 0–10V dimmers, and fan controls

Available finishes

Use **BOLD** color code in model number (Example: DV-600P-**BR**) Gloss finishes*







lvory



Gray



BR Brown



<u>BL</u> Black

Satin Colors® finishes*



** Stainless Steel wallplate only available separately and includes black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls. For wallplate information, see p.236

Dimmers



- Paddle turns on/off
- Slide up to brighten, down to dim
- C-L_® dimmers provide reliable dimming of dimmable CFLs/LEDs, as well as halogens and incandescents
- eco-dim_® model guarantees at least 15% energy savings compared to a standard switch*
- Locator light shines through paddle on select lighter colored models

♀ Incandescent/halogen dimmers

🖞 / 🖥 Dimmable CFL/LED (screw-base) dimmers

150W C·L dimmers

| 3-way/single-pole | DVCL-153P- XX 1 |
|---------------------------|-----------------------------|
| 120V 600W (Inc) 150W (CFI | _/LED) |
| 3-way/single-pole | DVSCCL-153P-XX ² |
| 120V 600W (Inc) 150W (CFI | _/LED) |

Visit **www.lutron.com/dimcflled** for an approved list of dimmable CFL/LED bulbs, and how to calculate wattage when mixing lamp types. Adjustable low-end trim.

- Incandescent/halogen dimmers
- ♥/♥ Dimmable CFL/LED (screw-base) dimmers
- Hi-Lume 1% 2-wire LED driver dimmers

250W C·L dimmers

| DVCL-253P-XX1 | | |
|--------------------------------------|--|--|
| 120V 600W (Inc) 250W (CFL/LED) | | |
| 350W (Hi-lume 1% LED driver, max. 8) | | |
| VSCCL-253P-XX ² | | |
| 120V 600W (Inc) 250W (CFL/LED) | | |
| 350W (Hi-lume 1% LED driver, max. 8) | | |
| | | |

Visit **www.lutron.com/dimcflled** for an approved list of dimmable CFL/LED bulbs, and how to calculate wattage when mixing lamp types. Adjustable low-end trim.

Incandescent/halogen dimmers

| Dimmers |
|---------|
|---------|

| Single-pole | DV-600P- XX 1 |
|-------------|-----------------------------------|
| 120V 600W | DVSC-600P- XX ² |
| Single-pole | DV-10P- XX 1 |
| 120V 1000W | DVSC-10P- XX ² |
| 3-way | DV-603P- XX 1 |
| 120V 600W | DVSC-603P- XX ² |
| 3-way | DV-103P- XX 1 |
| 120V 1000W | DVSC-103P- XX ² |

eco-dim_® dimmer

| 3-way/single-pole | DV-603PG- XX 3 |
|-------------------|-----------------------|
| 120V 600W | |

XX¹: Gloss color codes, see p.87

88

- XX²: Satin Colors® codes, see p. 87
- **XX**³: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA) Wallplates not included. Order separately, see p. 236

All models must be derated if ganged unless otherwise noted, see pp. 250–252 and 254.

Maximum light output of 85% guarantees 15% energy savings over standard switches