

Shown actual size: Rotary dimmer and 1-gang Fassada wallplate in White (WH).

Product family features

- The original electronic dimmer—first patented in 1959
- Easy-turn knob adjusts light to your favorite level
- eco-dim® model available
- Coordinating Fassada® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see p. 244

Control types

Single-pole (one location)

3-way or 4-way (two or more locations)

Direct load type compatibility

Incandescent/halogen lighting

Ceiling fans

Lighting load interfaces are not compatible with this family.

Available finishes

Use **BOLD** color code in model number (Example: D-600P-**IV**)

Gloss finishes*



WH
White



IV
Ivory

*Coordinating wallplates only available separately. For wallplate information, see p. 244.

Dimmer with rotate on/off knob



- Rotate on/off; rotate to adjust light level

Dimmers with push on/off knob



- Push on/off; rotate to adjust light level
- eco-dim® model guarantees at least 15% energy savings and triples lamp life compared to a standard switch*

Incandescent/halogen dimmer

Dimmer with rotate on/off knob	
Single-pole 120V 600W	D-600R-**XX**[1]

Incandescent/halogen dimmers

Dimmers with push on/off knob	
Single-pole 120V 600W	D-600P-**XX**[1]
3-way 120V 600W	D-603P-**XX**[1]

eco-dim® dimmer with push on/off knob	
3-way/single-pole 120V 600W	D-603PG-**XX**[1]

XX[1]: Gloss color codes, see p. 127
Wallplates not included. Order separately, see p. 244

All models must be derated if ganged, unless otherwise noted, see p. 253.

* Maximum light output of 85% guarantees 15% energy savings over standard switches