

Voice/Data/Video NEW!

VDV Scout® Pro 2 Series

Features	VDV Scout® Pro 2	VDV Scout® Pro 2 LT	
	VDV501-823 VDV501-824	VDV501-825 VDV501-826	
Tests RJ45 8-wire cables	●	●	
Tests RJ11/12 6-wire cables	●	●	
Tests F-connector coaxial cables	●	●	
Continuity testing	●	●	
Pass TIA-568A/B & crossover/uplink	●	●	
Wiremap	●	●	
Detects open faults	●	●	
Detects short faults	●	●	
Detects miswires	●	●	
Detects split pairs	●	●	
Measures cable length	—	●	
Supports up to 8 Test-n-Map™ Remotes	●	●	
ID	Supports up to 19 twisted-pair (RJ45) cable ID location remotes	●	●
	Supports up to 19 coaxial F-connector cable ID location remotes	●	●
Multiple-style Tone Generator†	4 Tones	4 Tones	
Low battery indicator	●	●	
Voltage warning	●	●	
Shield detection	●	●	
Apo Auto power off	●	●	



VDV501-824



VDV501-825



VDV501-826



VDV770-827

Items Included	Description	VDV Scout® Pro 2 Tester Kit	VDV Scout® Pro 2 Tester & Test-n-Map™ Remote Kit	VDV Scout® Pro 2 LT Tester & Remote Kit	VDV Scout® Pro 2 LT Tester & Test-n-Map™ Remote Kit	VDV Scout® Pro 2 Test-n-Map™ Remote Kit
	Cat. No.	VDV501-823	VDV501-824	VDV501-825	VDV501-826	VDV770-827
VDV Scout® Pro 2 Tester		●	●	—	—	—
VDV Scout® Pro 2 LT Tester		—	—	●	●	—
Test-n-Map™ Remotes		—	8	1	8	8
LanMap™ Cable Identification Location Remotes		5	—	19	—	—
CoaxMap™ Cable Identification Location Remotes		5	—	19	—	—
Coax barrel F adapter (female to female)		1	1	1	1	—
Coax push-on F adapter (threaded male to push-on female)		—	8	—	8	8
RJ45 jumper test cable (9")		—	8	—	8	8
9V battery		●	●	●	●	—
Carrying case		—	●	●	●	●

⚠ WARNING: Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

⚠ WARNING: Do NOT use on energized circuits or cabling systems.

Reference Guide

Cat. No.	UPC # 0-92644+	Description
FISH TAPES AND ACCESSORIES		
56055	56055-2	100' Multi-Groove Fiberglass Fish Tape – 7" leader
56056	56056-9	200' Multi-Groove Fiberglass Fish – 7" leader
56057	56057-6	50' Non-Conductive Multi-Groove Fiberglass Fish Tape
56058	56058-3	100' Non-Conductive Multi-Groove Fiberglass
56059	56059-0	200' Non-Conductive Multi-Groove Fiberglass
56000	56000-2	25' Steel Fish Tape
56001	56001-9	50' Steel Fish Tape
56002	56002-6	65' Steel Fish Tape
56003	56003-3	125' Steel Fish Tape
56004	56004-0	240' Steel Fish Tape
56005	56005-7	25' Steel Fish Tape
56006	56006-4	100' Steel Fish Tape
56007	56007-1	125' Stainless Steel Fish Tape
56008	56008-8	240' Stainless Steel Fish Tape
56013	56013-2	50' Spiral Steel Fish Tape
56065	56065-1	65' Steel Replacement Fish Tape
56125	56125-2	125' Steel Replacement Fish Tape
56240	56240-2	240' Steel Replacement Fish Tape
Pull Line		
56108	56108-5	500' Poly Pull Line
56110	56110-8	6500' Poly Pull Line
Lubricants		
51100	51100-4	Foam Wire Pulling Lubricant - 19 oz. can
Splinter-Guard™ Fish and Glow Rods		
56326	56326-3	Deluxe Fish Rod Kit
56304	56304-1	4' Lo-Flex Fish Rod
56306	56306-5	6' Lo-Flex Fish Rod
56312	56312-6	12' Lo-Flex Fish Rod Set
56324	56324-9	24' Lo-Flex Fish Rod Set
56325	56325-6	25' Fish and Glow Rod Set
56405	56405-5	5' Mid-Flex Glow Rod
56406	56406-2	6' Hi-Flex Glow Rod
56409	56409-3	9' Mid-Flex Glow Rod Set
56415	56415-4	15' Mid-Flex Glow Rod Set
56418	56418-5	18' Hi-Flex Glow Rod Set
56119	56119-1	Illuminated Fish Rod Tip
Conduit Benders		
56203	56203-7	Iron Bender w/ Handle – 1/2" EMT
56204	56204-4	Iron Bender w/ Handle – 3/4" EMT
56205	56205-1	Iron Bender w/ Handle – 1" EMT
56206	56206-8	Aluminum Bender w/ Handle – 1/2" EMT
56207	56207-5	Aluminum Bender w/ Handle – 3/4" EMT
56208	56208-2	1/2" Iron Conduit Bender Head
56209	56209-9	3/4" Iron Bender Head
56210	56210-5	1" Iron Bender Head
56211	56211-2	1-1/4" Iron Bender Head
51427	51427-2	Handle for 1/2" & 3/4" EMT Benders
51428	51428-9	Handle for 1" EMT Benders
51429	51429-6	Handle for 1-1/4" EMT Benders
VOICE/DATA/VIDEO TEST AND MEASUREMENT		
VDV501-828	58211-0	VDV Commander™ Test Kit
VDV501-829	58212-7	VDV Commander™ Test and Tone Kit
VDV501-815	58187-8	VDV Ranger™ TDR Kit
VDV501-823	58196-0	VDV Scout® Pro 2 Tester Kit
VDV501-824	58197-7	VDV Scout® Pro 2 Tester & Test-n-Map™ Remote Kit
VDV501-825	58198-4	VDV Scout® Pro 2 LT Tester & Remote Kit
VDV501-826	58199-1	VDV Scout® Pro 2 LT Tester & Test-n-Map™ Remote Kit
VDV770-827	58200-4	VDV Scout® Pro 2 Test-n-Map™ Remote Kit
VDV ProTech™ Kits		
VDV026-831	58248-6	ProTech™ Data Kit
VDV011-832	58249-3	ProTech™ Coaxial Kit
VDV001-833	58250-9	ProTech™ Data & Coaxial Kit

Cat. No.	UPC #0-92644+	Description
VDV Connectors		
VDV812-612	58148-9	Universal F Connector – RG6/6Q (50-Pack)
VDV812-618	58158-8	Universal F Connector – RG59 (50-Pack)
VDV813-613	58149-6	Universal BNC Connector – RG6/6Q (35-Pk)
VDV813-614	58150-2	Universal RCA Connector – RG6/6Q (35-Pk)
VDV813-619	58159-5	Universal BNC Connector – RG59 (35-Pk)
VDV813-620	58160-1	Universal RCA Connector – RG59 (35-Pk)
VDV812-624	58164-9	Standard F Connector – RG6 (50-Pk)
VDV826-600	58136-6	Telephone Plug – RJ11 – 6P6C (25-Pk)
VDV826-601	58137-3	Telephone Plug – RJ11 – 6P4C (25-Pk)
VDV826-602	58138-0	Modular Data Plug – RJ45 – CAT5e (50-Pk)
VDV826-603	58139-7	Modular Data Plug – RJ45 – CAT6 (25-Pk)
VDV826-604	58140-3	UY IDC Connector – UY 22-26 AWG (25-Pk)
VDV826-605	58141-0	UR IDC Connector – UR 19-26 AWG (25-Pk)
VDV826-611	58147-2	Modular Data Plug – RJ45 – CAT5e (100-Pk)
VDV826-628	58168-7	Modular Data – RJ45 – CAT5e (10-Pk)
ELECTRICAL TEST AND MEASUREMENT		
MM1300	69154-6	Electrician's/HVAC Multimeter
MM1300N	69654-1	Electrician's/HVAC Multimeter w/ NIST Cert.
MM2300	69155-3	Electrician's/HVAC TRMS Multimeter
MM2300N	69655-8	Electrician's/HVAC TRMS Multimeter w/ NIST Cert.
MM500	69158-4	Auto Ranging Multimeter
MM5000	69156-0	Electrician's TRMS Multimeter
MM5000N	69656-5	Electrician's TRMS Multimeter w/ NIST Cert.
MM6000	69157-7	Electrician's / HVAC TRMS Multimeter
MM6000N	69657-2	Electrician's / HVAC TRMS Multimeter w/ NIST Cert.
CL1200	69212-3	600A AC Clamp Meter
CL1200N	69712-8	600A AC Clamp Meter w/ NIST Cert.
CL2200	69214-7	600A AC/DC True RMS Clamp Meter
CL2200N	69714-2	600A AC/DC True RMS Clamp Meter w/ NIST Cert.
CL2300	69215-4	600A AC/DC TRMS Clamp Meter w/ Temp.
CL2300N	69715-9	600A AC/DC TRMS Clamp Meter w/ Temp.w/ NIST Cert.
CL2500	69207-9	1000A AC/DC TRMS Clamp Meter
CL2500N	69707-4	1000A AC/DC TRMS Clamp Meter w/ NIST Cert.
CL3200	69208-6	200A AC Fork Tester
CL3200N	69708-1	200A AC Fork Tester w/ NIST Cert.
IR2000A	69309-0	Infrared Thermometer
NCVT-2	69002-0	Dual Range Non-Contact Voltage Tester
69416	69416-5	Silicone Test Leads
PERSONAL PROTECTIVE EQUIPMENT		
Protective Eyewear		
60046	60046-3	Standard Eyewear – Dark Gray Lens
60047	60047-0	Standard Eyewear – SCT Gray Lens
60049	60049-4	Standard Eyewear – Amber Lens
60053	60053-1	Standard Eyewear – Clear
60054	60054-8	Standard Eyewear – Clear
60055	60055-5	Standard Eyewear – Espresso
60056	60056-2	Frameless Eyewear – Clear
60057	60057-9	Frameless Eyewear – Espresso
Hard Hats and Accessories		
60009	60009-8	Standard Hard Cap, White
60010	60010-4	Standard Hard Cap, Yellow
60011	60011-1	Standard Hard Cap, Blue
60025	60025-8	Advance® Hard Cap, White
60027	60027-2	Advance® Hard Cap, Blue
60028	60028-9	V-Gard® Hard Hat, White
60030	60030-2	V-Gard® Hard Hat, Blue
60031	60031-9	V-Gard® Hard Hat, White
60060	60060-9	Full Face Shield
Lockouts, Barricade Tape and Cleaners		
45200	45200-0	Lockouts w/Interlocking Tabs
45201	45201-7	Lockouts w/Interlocking Tabs
58000	58000-0	200' CAUTION Tape
58001	58001-7	1000' CAUTION Tape
58002	58002-4	200' CAUTION/BURIED ELECTRIC LINE Tape