

High Strength 1/4" Wide Steel Fish Tapes



Additional Features:

- Permanent, laser etched 1' increments on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.
- Tempered, high quality tape keeps its stability as it glides between surfaces for effective pushing and pullings of wire under carpets, through insulated walls and over suspended ceilings.
- 25' length is perfect for short wire runs associated with light commercial, residential and voice-data-video-audio installations (Cat. No. 56005).



NEW!

56005

56005 Has a No Snag Plastic Tip



1' Permanent Laser Etched Descending Increments.

Cat. No.	Tape Size	Reel Diameter	Weight (lbs.)
56005	25' L x 1/4" W x .030" H (7 m L x 6.3 mm W x .7 mm H)	7" (178 mm)	1.1
56006	100' L x 1/4" W x .062" H (30 m L x 6.3 mm W x 1.5 mm H)	13" (330 mm)	6.8

High Strength Stainless Steel Fish Tapes



Additional Features:

- Permanent, laser etched 1' increments on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.
- Stainless Steel fish tape is corrosion resistant and extends the life of the tool.
- High strength spring steel fish tapes are stiff for long runs and are great for heavy duty wire pulls.



NEW!

56008

Cat. No.	Tape Size	Reel Diameter	Weight (lbs.)
56007	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7
56008	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5



1' Permanent Laser Etched Descending Increments.

Fiberglass Fish Tapes



Additional Features:

- Designed for flexibility and easy navigation through conduit runs.
- Non conductive, composite fish tape slides easily over existing wires and through multiple bends.
- The lightweight and strong fiberglass composite tape resists harsh elements and is strength rated up to 500 pulling pounds.
- The 13" case diameter means you can reel in 15% more tape in a single revolution vs. a standard 12" case.
- Durable 7" leader helps push through crowded conduit.



Repair kit available (Cat. No. 56115).



NEW!

56010

Cat. No.	Tape Size	Reel Diameter	Weight (lbs.)
56009	50' L x 3/16" W (7" leader) (15 m L x 4.8 mm W)	13" (330 mm)	2.8
56010	100' L x 3/16" W (7" leader) (30 m L x 4.8 mm W)	13" (330 mm)	3.5

All dimensions are in inches and (millimeters) unless otherwise specified.

⚠WARNING: Wear approved eye protection when feeding, pulling or rewinding fish tape.

⚠WARNING: Never remove screws while fish tape is coiled inside reel.

⚠WARNING: Do NOT use any fish tape on or near live circuits. Use extreme caution when working near any electrical equipment.

⚠WARNING: Use a safe work position to avoid loss of balance when using fish tape.



Fish Tapes

Features:

13" case diameter allows you to reel in 15% more tape in a single revolution than similar sized 12" tapes saving you time and effort.

Raised fingergrrips help transfer 100% of the winding power from your hand and fingers.



The unique sloped handle optimizes the position of your hand for quick hand-over-hand rewinds and allows a more level payout of tape on the backswing while feeding conduit.

Polypropylene case and handle are extremely durable and offer the maximum in shock and impact resistance.

Round inner ring design provides a smooth, consistent and comfortable surface for winding and rewinding.

High Strength 1/8" Wide Steel Fish Tapes

**DEPTH
FINDER™**

NEW!

Additional Features:

- *Permanent, laser etched 1' increments on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.*
- *Full grip style handle gives you a firm, steady grip as you pull tape from the case (Cat. Nos. 56000, 56001).*
- *The 13" case diameter means you can reel in 15% more tape in a single revolution than similar sized 12" tapes saving you time and effort (Cat. Nos. 56003, 56004).*



Cat. No.	Tape Size	Reel Diameter	Weight (lbs.)
56000	25' L x 1/8" W x .045" H (7 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.0
56001	50' L x 1/8" W x .045" H (15 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.3
56002	65' L x 1/8" W x .062" H (19 m L x 3 mm W x 1.5 mm H)	9" (229 mm)	2.6
56003	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7
56004	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5



All dimensions are in inches and (millimeters) unless otherwise specified.

▲WARNING: Wear approved eye protection when feeding, pulling or rewinding fish tape.

▲WARNING: Never remove screws while fish tape is coiled inside reel.

▲WARNING: Do NOT use any fish tape on or near live circuits. Use extreme caution when working near any electrical equipment.

▲WARNING: Use a safe work position to avoid loss of balance when using fish tape.

