

3M™ Heat Shrink Heavy Duty End Caps SKE


3M Heat Shrink End Caps provide a reliable and easy method of sealing cables for both indoor and outdoor applications whilst offering excellent electrical and mechanical protection. Internal adhesive helps to form a watertight seal. The materials used are halogen free.

Applications: Insulating/sealing of cable ends for indoor and outdoor applications



Product	3M Order Code	Cable Diameter	Expanded Diameter	Fully Recovered Dimensions		
				Diameter	Length	Wall Thickness
SKE 4/10	DE272919635	4 - 8 mm	10 mm	4 mm	40 mm	2.5 mm
SKE 8/20	DE272919643	8 - 16 mm	20 mm	8 mm	65 mm	2.5 mm
SKE 15/40	DE272919718	15 - 32 mm	40 mm	15 mm	105 mm	3.0 mm
SKE 25/63	DE272919650	25 - 51 mm	63 mm	25 mm	160 mm	4.5 mm
SKE 30/76	DE272919668	30 - 61 mm	76 mm	30 mm	140 mm	4.5 mm
SKE 45/100	DE272919676	45 - 80 mm	100 mm	45 mm	160 mm	4.0 mm
SKE 61/158	DE272919767	61 - 126 mm	158 mm	63 mm	190 mm	4.0 mm

Cable Diameter (mm)



Heat Shrink Part Numbers

SKE 4/10	4 - 8
SKE 8/20	8 - 16
SKE 15/40	15 - 32
SKE 25/63	25 - 51
SKE 30/76	30 - 61
SKE 45/100	45 - 80
SKE 61/158	61 - 126

3M™ Heat Shrink Cable Breakouts

3M Heat Shrink Cable Breakouts are designed for quick and easy insulation and sealing of cable breakout areas, and provide resistance to abrasion, weathering and chemical attack. The parts are made from semi-rigid, cross-linked modified polyolefin material that is coated internally with hot melt adhesive. The materials used are halogen free. On application of heat the adhesive melts and the part shrinks forming a watertight seal.

Applications: Cable breakout area sealing



Product	3M Order Code	Description	Conductor Size Range (LV cable)	Neck Expanded Diameter	Neck Recovered Diameter	Finger Expanded Diameter	Finger Recovered Diameter	Recovered Length	Neck Recovered Wall Thickness	Finger Recovered Wall Thickness
SKE-3F/1-1.5	DE272919734	3 way outlet	6 - 16 mm ²	25 mm	9 mm	9 mm	3 mm	70 mm	2.5 mm	1.8 mm
SKE-3F/2	DE272919577	3 way outlet	10 - 50 mm ²	35 mm	15 mm	13 mm	4 mm	100 mm	2.5 mm	1.8 mm
SKE-3F/4	DE272919684	3 way outlet	50 - 150 mm ²	55 mm	23 mm	30 mm	8 mm	170 mm	3.5 mm	2.7 mm
SKE-3F/5	DE272919783	3 way outlet	185 - 400 mm ²	110 mm	35 mm	50 mm	17 mm	215 mm	3.5 mm	3.5 mm
SKE-3F/6	DE272919817	4 way outlet	-	110 mm	35 mm	50 mm	17 mm	215 mm	3.5 mm	3.5 mm
SKE-4F/1+2	DE272919528	4 way outlet	4 - 35 mm ²	35 mm	15 mm	15 mm	4 mm	100 mm	3.8 mm	1.8 mm
SKE-4F/3+4	DE272919536	4 way outlet	25 - 150 mm ²	57 mm	23 mm	30 mm	6 mm	170 mm	4.0 mm	3.0 mm
SKE-4F/5	DE272919601	4 way outlet	120 - 400 mm ²	95 mm	36 mm	38 mm	14 mm	220 mm	3.5 mm	2.5 mm