

Single (Thin) Wall Tubing: 3M™ FP-301 Thin-Wall Tubing



3M™ Heat Shrink Thin-Wall Tubing FP-301 (1/8 Inch)

Ordering Size: 1/8" (3,18 mm)

Expanded I.D. (Min.): 0.125" (3,18 mm)

Recovered I.D. (Max.): 0.062" (1,57 mm)

Recovered Wall Thickness (Nominal): 0.020" (0,51 mm)

Material	Polyolefin
Shrink Ratio	2:1
Operating Temperature	-67 to 275°F (-55 to 135°C)
Voltage	600 Volts Max.
RoHS 2011/65/EU	Yes
Application Specifications	SAE-AMS-DTL-23053/5, Class 1, 2; AMS-3636, AMS-3637
Agency Approvals	
Manufacturing Origin	



Order No.	UPC	Color	Format	Flame Retardant	Case Qty.
FP301-1/8-6"-Black-10-10 Pc Pks	051128-60116	Black	6" (152,4 mm) pieces	Yes	10/pk, 10 pks
FP301-1/8-6"-Black-200 Pcs	051128-59889	Black	6" (152,4 mm) pieces	Yes	200 pcs
FP301-1/8-6"-Clear-10-10 Pc Pks	051128-60117	Clear	6" (152,4 mm) pieces	No	10/pk, 10 pks
FP301-1/8-48"-Black-25 Pcs	051128-59979	Black	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-Black-250 Pcs	051128-59828	Black	48" (1,22 m) sticks	Yes	250 pcs
FP301-1/8-48"-Blue-25 Pcs	051128-59984	Blue	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-Clear-25 Pcs	051128-59980	Clear	48" (1,22 m) sticks	No	25 pcs
FP301-1/8-48"-Clear-250 Pcs	051128-59850	Clear	48" (1,22 m) sticks	No	250 Pcs
FP301-1/8-48"-Green-25 Pcs	051128-59985	Green	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-Red-25 Pcs	051128-59982	Red	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-White-25 Pcs	051128-59981	White	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-Yellow-25 Pcs	051128-59983	Yellow	48" (1,22 m) sticks	Yes	25 pcs
FP301-1/8-48"-Black-Hdr-25 Pcs	051128-59640	Black	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-48"-Blue-Hdr-25 Pcs	051128-59645	Blue	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-48"-Clear-Hdr-25 Pcs	051128-59641	Clear	48" (1,22 m) sticks w/ Hdr Label	No	25 pcs
FP301-1/8-48"-Green-Hdr-25 Pcs	051128-59646	Green	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-48"-Red-Hdr-25 Pcs	051128-59643	Red	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-48"-White-Hdr-25 Pcs	051128-59642	White	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-48"-Yellow-Hdr-25 Pcs	051128-59644	Yellow	48" (1,22 m) sticks w/ Hdr Label	Yes	25 pcs
FP301-1/8-25'-Black-Reel	054007-40060	Black	25' (7,62 m) reel	Yes	1 reel
FP301-1/8-100'-Black-Spool	051135-35562	Black	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-Blue-100'	051135-35565	Blue	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-100'-Clear-Spool	051135-35567	Clear	100' (30,48 m) spool	No	3 spools
FP301-1/8-Green-100'	051135-37593	Green	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-Red-100'	051135-35564	Red	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-White-100'	051135-35563	White	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-Yellow-100'	051135-35566	Yellow	100' (30,48 m) spool	Yes	3 spools
FP301-1/8-500'-Black-Spool	054007-08472	Black	500' (152,40 m) spool	Yes	3 spools
FP301-1/8-500'-Clear-Spool	054007-08526	Clear	500' (152,40 m) spool	No	3 spools