

TYPE

DBK

ASK

Direct Burial and Above Grade Splice Kits



- DBK-1 connectors manufactured from electrolytic
- All other connectors manufactured from high strength aluminum alloy
 Heavy wall heat shrink tubing with sealant
- Connector and heat shrink packaged together
 UL Listed, rated for 600 volts, 90° C

Benefits

- Provides maximum conductivity for UF cable
- Provides high conductivity and can be used with either aluminum or copper conductors
 Provides watertight splice. Kits with heat shrink are
- designed to withstand abrasions due to direct burial in rocký soil.
- Provides ease of ordering
- Ensures reliability









Fig. 3

Catalog Number	Figure Number	UF Cable Range Minimum Maximum		Wire Range	Testing Certification			
DBK-1	1	14/2 with Ground	8/3 with Ground	•	ULSTED SSX4			
DBK-2	2			2-8	UNTED 88X4			
DBK-250	2			250kcmil-1	ULSTED SSX4			
Tested UL 486D, UL File E125087 ABOVE GRADE SPLICE KITS								

ASK-2*	3	-	-	2-8	ULSTED 4556	Н
ASK-250*	3		-	250kcmil-1	ULSTED 4536	

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG) *Not UL Listed for direct burial.

Tested to UL 486A/B, UL File E6207

