


Nylon 6/6 Type CT-MH Mounting Hole Cable Ties

UNIRAP™ Mounting Hole Cable Ties

Type CT-MH

Bundling and mounting, one easy installation. Ideal for use where bundle needs to be secured, such as control panels and ceilings. Can be bundled before or after mounting.



G-12

| Std Pkg Catalog Number | Color | Screw Size | Max Bundle Diameter In. [mm] | Min Tensile Strength (lbs) | Length Inches [mm] | Width Inches [mm] | Tool | Tool Setting (if applicable) | Bulk Catalog Number |
|------------------------|----------|------------|------------------------------|----------------------------|--------------------|-------------------|-----------|------------------------------|---------------------|
| CT18075MH4C | Natural | #4 | 0.75 [19.1] | 18 | 3.93 [100] | 0.10 [3.0] | CTT50 MK9 | 2 Std. | CT18075MH4M |
| CT30125MH8C | Natural | #8 | 1.25 [31.8] | 30 | 6.80 [173] | 0.14 [4.0] | CTT50 MK9 | 2 Std. | CT30125MH8M |
| CT30125MH8M0* | UV Black | | | | | | | | — |
| CT50175MH10C | Natural | #10 | 1.75 [44.5] | 50 | 8.10 [206] | 0.18 [5.0] | CTT50 MK9 | 3 Heavy | CT50175MH10M |
| CT50175MH10C0 | UV Black | | | | | | | | CT50175MH10M0 |
| CT50400MH10C | Natural | #10 | 4.00 [101.6] | 50 | 15.10 [384] | 0.18 [5.0] | CTT50 MK9 | 3 Heavy | — |
| CT50400MH10C0 | UV Black | | | | | | | | CT50400MH10M0 |
| CT120400MH14L | Natural | 1/4" | 4.00 [101.6] | 120 | 15.70 [399] | 0.30 [8.0] | MK9 | Heavy | CT120400MH14D |
| CT120400MH14L0 | UV Black | | | | | | | | CT120400MH14D0 |

*Only available in Bulk Package of 1000 pieces.