


[On Line Catalog](#)
**BURNDY Catalog Number**

YAL6CT14

**UPC Number**

7818104175844

**Description**

CANLUG- 6 STR-SHORT-1/4

**Status**

Active

**Web Use**

BURNDY Product Line

**Tongue Angle**

Straight

**Length (in)**

1.58

**Barrell Style**

Chamfered

**Bolt Hole Size (in)**

0.27

**Barrel Type**

Standard

**Thickness**

0.08

**B Length (in)**

0.75

**Pad Width (in)**

0.45

**Dimensional****Number of Holes**

1

**Product Description**Copper Compression Lug, 1 Hole  
w/ Inspection Window, 6 AWG,  
1/4" Stud, Short Barrel, Tin Plated**General****Conductor(s)****Flex (Class G) Size - Range**

N/A

**Flex (Class H) Size - Range**

N/A

**Flex (Class I) Size - Range**

N/A

**Copper Solid Size (Range)**

N/A

**DLO Size (Range)**

N/A

**Copper Stranded (Range)**

6 AWG

**Physical****Type of Plating**

Tin - Electro Plated

**Bolt Hole Size**

1/4

**Color Code**

Blue

**Plated (Yes or No)**

Y

**Index Number**

7

**Product Material**

Copper

**Approvals / Certifications****UL Listed**

Y

**CSA Certified**

Y

**ROHS Compatible**

Compliant

**UL Recognized**

N

**CULUS**

N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175