



BURNDY Catalog Number YAL2CT516
UPC Number 78181041719
Description CANLUG-#2 STR-SHORT-5/16
Status null

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	1.65
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.33
Barrel Type	Standard
Thickness	0.11
B Length (in)	0.7
Pad Width (in)	0.61
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	2
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	5/16
Color Code	Brown
Plated (Yes or No)	Y
Index Number	10
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services
47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175