

Compact Fluorescent Lamps

PL-T Lamps

Watts	Bulb Base	Product Number	Symbols, Footnotes	Description	Generic Designation	Pkg. Qty.	MOL (In.)	Rated Avg. Life (Hrs.) (230)	Design Lumens (208)	CRI	Brightness (Lumens) (231)	Life (Yrs.) (446)	Energy Cost (445)	Light Appear. (CCT)
PL-T (Triple) 4-Pin Amalgam, Energy Advantage											FTC REQUIREMENTS ^Y			
21	PL-T GX24q-3	40779-1	●	PL-T 26W/830/XEW/A/4P/ALTO 21W	CFTR26W/GX24q/830	10	5	16,000	1235	82	1400	14.6	\$2.53	3000
27	PL-T GX24q-3	22021-0	●	PL-T 32W/830/XEW/A/4P/ALTO 27W	CFTR32W/GX24q/830	10	5½	16,000	1725	82	1875	14.6	\$3.25	3000
		22022-8	●	PL-T 32W/835/XEW/A/4P/ALTO 27W	CFTR32W/GX24q/835	10	5½	16,000	1725	82	1875	14.6	\$3.25	3500
		22024-4	●	PL-T 32W/841/XEW/A/4P/ALTO 27W	CFTR32W/GX24q/841	10	5½	16,000	1725	82	1875	14.6	\$3.25	4100
33	PL-T GX24q-4	22026-9	●	PL-T 42W/830/XEW/A/4P/ALTO 33W	CFTR42W/GX24q/830	10	6¾	16,000	2400	82	2615	14.6	\$3.97	3000
		22028-5	●	PL-T 42W/835/XEW/A/4P/ALTO 33W	CFTR42W/GX24q/835	10	6¾	16,000	2400	82	2615	14.6	\$3.97	3500
		22029-3	●	PL-T 42W/841/XEW/A/4P/ALTO 33W	CFTR42W/GX24q/841	10	6¾	16,000	2400	82	2615	14.6	\$3.97	4100

PL-T (Triple) 4-Pin Amalgam

18	PL-T GX24q-2	45819-0	●	PL-T 18W/827/A/4P/ALTO	CFTR18W/GX24q/827	10	4¾	16,000	1020	82	1200	14.6	\$2.17	2700
		45821-6	●	PL-T 18W/830/A/4P/ALTO	CFTR18W/GX24q/830	10	4¾	16,000	1020	82	1200	14.6	\$2.17	3000
		45822-4	●	PL-T 18W/835/A/4P/ALTO	CFTR18W/GX24q/835	10	4¾	16,000	1020	82	1200	14.6	\$2.17	3500
		45823-2	●	PL-T 18W/841/A/4P/ALTO	CFTR18W/GX24q/841	10	4¾	16,000	1020	82	1200	14.6	\$2.17	4100
26	PL-T GX24q-3	45824-0	●	PL-T 26W/827/A/4P/ALTO	CFTR26W/GX24q/827	10	5	16,000	1530	82	1800	14.6	\$3.13	2700
		45825-7	●	PL-T 26W/830/A/4P/ALTO	CFTR26W/GX24q/830	10	5	16,000	1530	82	1800	14.6	\$3.13	3000
		45826-5	●	PL-T 26W/835/A/4P/ALTO	CFTR26W/GX24q/835	10	5	16,000	1530	82	1800	14.6	\$3.13	3500
		45827-3	●	PL-T 26W/841/A/4P/ALTO	CFTR26W/GX24q/841	10	5	16,000	1530	82	1800	14.6	\$3.13	4100
32	PL-T GX24q-3	45828-1	●	PL-T 32W/827/A/4P/ALTO	CFTR32W/GX24q/827	10	5½	16,000	2040	82	2400	14.6	\$3.85	2700
		45829-9	●	PL-T 32W/830/A/4P/ALTO	CFTR32W/GX24q/830	10	5½	16,000	2040	82	2400	14.6	\$3.85	3000
		45830-7	●	PL-T 32W/835/A/4P/ALTO	CFTR32W/GX24q/835	10	5½	16,000	2040	82	2400	14.6	\$3.85	3500
		45831-5	●	PL-T 32W/841/A/4P/ALTO	CFTR32W/GX24q/841	10	5½	16,000	2040	82	2400	14.6	\$3.85	4100
42	PL-T GX24q-4	14900-5	●	PL-T 42W/827/A/4P/ALTO	CFTR42W/GX24q/827	10	6¾	16,000	2720	82	3200	14.6	\$5.06	2700
		14901-3	●	PL-T 42W/830/A/4P/ALTO	CFTR42W/GX24q/830	10	6¾	16,000	2720	82	3200	14.6	\$5.06	3000
		14902-1	●	PL-T 42W/835/A/4P/ALTO	CFTR42W/GX24q/835	10	6¾	16,000	2720	82	3200	14.6	\$5.06	3500
		14903-9	●	PL-T 42W/841/A/4P/ALTO	CFTR42W/GX24q/841	10	6¾	16,000	2720	82	3200	14.6	\$5.06	4100
57	PL-T GX24q-5	14632-4	●	PL-T 57W/835/A/4P	CFTR57W/GX24q/835	10	7¾	16,000	3741	82	4300	14.6	\$6.87	3500
		14633-2	●	PL-T 57W/841/A/4P	CFTR57W/GX24q/841	10	7¾	16,000	3741	82	4300	14.6	\$6.87	4100

For the most current product information, go to the e-catalog on www.philips.com. Compact fluorescent symbols and footnotes located on page 63.

Philips PL-T

Limited Warranty Period:
18 months*

Philips PL-T

Energy Advantage

Limited Warranty Period:
24 months*

* Certain limitations and conditions apply. See Philips for further warranty details.

