

***Ty-Fast<sup>®</sup>***  
***Safe-Ty<sup>®</sup>***  
***Ty-Met<sup>®</sup>***  
***Ty-Rap<sup>®</sup>***

Cable Ties



**Quality Cable  
Ties for Special  
Applications**

***Thomas & Betts***

## Ty-Fast® Standard Cable Ties

Ty-Fast® one piece cable ties offer an economical alternative made from quality nylon 6/6 (natural or UV stabilised black). Rated temperature range from 85°C to 40°C. The smooth edges are designed to prevent damage to wire insulation. Ty-Fast cable ties may be fastened with all standard Thomas & Betts cable tie tools.



### Standard Cable Ties

Std. Pk. Cat. No.	Body Width (mm)	Length (mm)	Max. Wire Bundle Dia. (mm)	Tensile Strength (kg)	Bulk Pk. Qty.
TY075-18	2.40	104	19.05	8	1000
TY125-18	2.40	168	40.00	8	1000
TY125-40	3.60	150	31.75	18	1000
TY175-50	4.80	182	44.45	22	1000
TY200-18	2.40	204	50.80	8	1000
TY200-40	3.60	206	50.80	18	1000
TY200-120	7.60	280	76.00	54	500
TY300-40	3.60	304	76.20	18	1000
TY300-50	4.80	307	76.20	22	1000
TY400-50	4.80	370	101.60	22	1000
TY400-120	7.60	380	101.60	54	500
TY500-50	4.80	430	120.00	22	100

Add -100 to Part No. for 100 pack (eg TY075-18-100) Add X to Cat. No. for Outdoor Black UV stabilised 6/6 Nylon (eg TY075-18X-100)

## Safe-Ty® Low Profile In-Line Fasteners

This new Safe-Ty® design from Thomas & Betts is ideal for use where precision bundling is required and clearance is a necessity. A unique saddle back design curves to form a snug fit around the bundle, and allows for easy pull-through in bulkheads and any tight spaces. Our contoured head eliminates snagging and sharp edges are reduced by our safe-guard walls.



### Low Profile In-Line Fasteners

Std. Pk. Cat. No.	Body Width (mm)	Length (mm)	Max. Wire Bundle Dia. (mm)	Tensile Strength (kg)	Bulk Pk. Qty.
SF100-18	2.4	118	25.4	8	1000
SF100-18X	2.4	118	25.4	8	1000
SF175-50	4.8	195	44.4	22	1000
SF175-50X	4.8	195	44.4	22	1000
SF300-50	4.8	288	76.2	22	1000
SF300-50X	4.8	288	76.2	22	1000
SF400-50	4.8	369	101.6	22	1000
SF400-50X	4.8	369	101.6	22	1000
SF400-120	7.6	370	101.6	54	500
SF400-120X	7.6	370	101.6	54	500
SF600-120	7.6	533	152.4	54	500
SF600-120X	7.6	533	152.4	54	500

Material: Natural Nylon 6/6 (X suffix is weatherable black nylon)  
For 100 packs add suffix - 100 eg: SF175-50X-100

## Ty-Met® 316 Stainless Steel Ball Lock Ties

Thomas & Betts stainless steel ties are self-locking, requiring no time consuming crimping or folding operations. The strong locking mechanism, incorporating a steel ball, has a low insertion force while the strap section has rounded edges and smooth surfaces making the ties ideal for fast, safe, hand installation.



### Fast, easy installation

Std. Pk. Cat. No.	Body Width (mm)	Length (mm)	Max. Wire Bundle Dia. (mm)	Tensile Strength (kg)	Std. Pk. Qty.
LSY-4.6-100B	4.6	100	16	45	100
LSY-4.6-150B	4.6	150	32	45	100
LSY-4.6-200B	4.6	201	51	45	100
LSY-4.6-360B	4.6	360	102	45	100
LSY-4.6-520B	4.6	520	152	45	100
LSY-4.6-680B	4.6	679	203	45	100
LSY-4.6-840B	4.6	838	254	45	100
LSY-4.6-1000B	4.6	1000	300	45	100
LSY-7.9-100B	7.9	100	16	113	100
LSY-7.9-150B	7.9	150	32	113	100
LSY-7.9-200B	7.9	201	51	113	100
LSY-7.9-360B	7.9	360	102	113	100
LSY-7.9-520B	7.9	520	152	113	100
LSY-7.9-680B	7.9	679	203	113	100
LSY-7.9-840B	7.9	838	254	113	100
LSY-7.9-1010B	7.9	1010	318	113	100
LSY-7.9-1200B	7.9	1200	370	113	100
LSY-7.9-1300B	7.9	1300	400	113	100
LSY-7.9-1400B	7.9	1400	435	113	100

- Mounting Bases
- Brackets & Supports
- Identification Plates
- Installation Tools
- Marking Pens
- Clamps & Spacers



**ORDERS HOTLINE**

**PH 1300 666 595**  
**FX 1300 666 594**