

4 in. Octagonal Boxes

Nonmetallic Sheathed Cable Clamps





Prepositioned depth tabs recessed 1/2 in.



BC54151-LB

Side bracket, with holding prongs and prepositioned depth tabs.



BC54151-LD

Swing-arm" rework brackets. Max. wall thickness: 3/4 in.. Max. load capacity: 12 lb. (5.5 kg).



BC54171-I

Side bracket, with holding prongs.



BC54171-LB

Side bracket, with holding prongs.



CI54171-LF

Ceiling fan box. (Supplied with 2 #10-32 machine screws and star washers.) Max. load capacity: 35 lb. (15.6 kg).



Cat. No.	Volume (Cu. in.)	Features		Knockouts		Pryouts	
		Bracket	Raised Ground Screw	1/2 in. sides	1/2 in. bottom	sides	bottom
1-1/2 in. Deep							
BC54151-L	15.0	-	yes	2	1	4	4
BC54151-LB	15.0	"B"	yes	1	1	4	4
BC54151-LD	15.0	rework	yes	-	1	4	4
CI54151-LF	15.0	-	yes	2	1	4	4
2-1/8 in. Deep							
BC54171-L	21.0	-	yes	2	1	4	4
BC54171-LB	21.0	"B"	yes	1	1	4	4
BC54171-LD	21.0	rework	-	-	1	4	4
CI54171-LF	21.0	-	yes	2	1	4	4

FOR USE WITH NONMETALLIC SHEATHED CABLE ONLY

Note: CEC 2012 rule 30-302: Subrule (4) requires that a ceiling-mounted luminaire weighing 23 kg or less be supported on a ceiling outlet box attached directly to the building structure. A bar hanger may also be used to attach a ceiling outlet box to the building structure when the luminaire weighs 23 kg or less.

