## *Iberville*°

## Boxes and Covers

## **Device Boxes**

## **Conduit Knockouts**

| CI1104-K   | BC1104-LE  | CI1104-SB  | BCR2000        |
|--|--|--|----------------|
| Concentric knockouts. Recessed ears.   | Less ears.   | CI1104-3B  |                |
|  | 8.   | 8  |                |
| CI3104-KSSX  | BC3104-KSS1X-1   | CI3104-SSX   | CI1004         |
| Concentric knockouts. "Wraparound" bracket<br>for 2-1/2 in. and 3-5/8 in. steel studs. With<br>integral support bracket. | Concentric knockouts. "Wraparound" bracket<br>for 2-1/2 in. and 3-5/8 in. steel studs. With<br>integral support bracket. Brackets positioned<br>for 2 layers of 1/2 in. Drywall. | "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. | Recessed ears. |
|  |  |  | (SP°           |

. . . . . . . . . . . . . . . .

| Cat. No.                             | Volume                | Features |              | Knockouts    |                |              |
|--------------------------------------|-----------------------|----------|--------------|--------------|----------------|--------------|
|                                      | (Cu. in.)             | Ears     | Bracket      | 1/2 in. ends | 1/2 in. bottom | 3/4 in. ends |
| 2 in. Deep — Gangable — 3 in. x 2 ir | ı.                    |          |              |              |                |              |
| СІ1104-К                             | 12.5                  | recessed | -            | 2            | 2              | 2            |
| BC1104-LE                            | 12.5                  | -        | -            | 2            | 2              | -            |
| CI1104-SB                            | 12.5                  | -        | "SB"         | 2            | 2              | -            |
| CI3104-KSSX                          | 16.0                  | -        | "SSX"        | 2            | 2              | 2            |
| BC3104-KSS1X-1                       | 16.0                  | -        | "SSX"        | 2            | 2              | 2            |
| CI3104-SSX                           | 16.0                  | -        | "SSX"        | 2            | 2              | -            |
| 3 in. Deep — Gangable — 3 in. x 2 ir | 1                     |          |              |              |                |              |
| CI1004                               | 15.0                  | recessed | -            | 2            | 2              | -            |
| CI3004-KSSX-1.25                     | 18.0                  | -        | "SSX"        | -            | 1              | 2            |
| Cat. No.                             | Volume<br>(Cu. in.)   | Usage    | Ground Screw | Knockout     |                |              |
| 2 in. Deep — Non-Gangable — 3-3/4    | 1 in. x 4 in. x 2 in. |          |              |              | New            |              |
| BCR2000*                             | 18.0                  | KO       | 2            | 2            |                |              |

